







Upper part and bottom part
Material: Polyamide
Color: black, similar RAL 9011

Operating position I (Measured at start position) ≈ 2.3mm
Operating position II (Measured at start position) ≈ 8mm
Measured at outer edge of upper part



Schematic




Single pole change-over
Single pole normally closed

Marking

© MARQUARDT
2410.0101 μ
6(2.5)/250~50E3

Schematic



-	-	-	2410.0101-XX
Figure	Type	Customer Part No.	Art.No.-Pl
Shape and location © =	Angle ± ° Edge tolerance Length Radii	Sheet 01	Ident. Document number Index
		Format DIN A2	K 24100101 I
		Projection Scale 1:1	Foot Pressure Switch
		All dimensions are in millimetres	
i	137878	2022-02-01	KELBOUSSIM
k	131778	2020-11-05	THAKARES
j	41282	2004-10-21	BZ
i	30220	2000-09-27	PFU
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by
		System NX V1872	Replacement of
		Zg.gl.Nr.v.26.04.1994	
		MARQUARDT	