







Upper part and bottom part:
Material: Polyamide
Color: black, similar RAL 9011



Schematic




Single pole normally open

Marking

© MARQUARDT
2410.0301 μ
6(2.5)/250~50E3

Schematic



Operating position at the travel of (measured at start position) ~ 8 mm measured at outer edge of upper part

-		-				-		2410.0301-XX		
Figure		Type				Customer Part No.		Art.No.-PI		
Shape and location	Angle ± 2 °	Length				Radii				
		0-6	± 0.15		±	0-6	±			
	Edge tolerance	>6-15	± 1		±	>6-15	±			
		>15-30	± 1		±	>15-30	±			
		>30-70	± 1.5		±	>30-70	±			
		>70-120	± 1.5		±	>70-120	±			
		>120-200	± 1.5		±	>120-200	±			
		±			±	±				
		±			±	±				
		±			±	±				
⊙ =										
h	137878	2022-02-01		KELBOUSSIM		Sheet 01 Format DIN A2 Projection  Scale 1:1 All dimensions are in millimetres		Ident. K	Document number 24100301	Ind
g	131778	2020-11-09		THAKARES						
f	30220	2000-09-28		PFU				System NX V1872	Foot Pressure Switch	 MARQUARDT
e	23889	1996-05-08		MOO						
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by		Zg.gl.Nr.v.23.07.1997					