

# Han-Eco® B Wave 2



Pushing Performance



Description	Links to Other Materials
-------------	--------------------------

Han-Eco® B Wave 2 is the addition of the covers, Cable to Cable and Surface Mount Housing variants.

- [Han Eco B Landing Page](#)
- [Han Eco B eCatalog](#)

Specs	
-------	--

- IEC61984 Connectors
- IEC61373
- IP 65 and IP66
- Gland size: M25, M30, M40

- Temp Range: -40C to +125C
- Fiber glass reinforced polyamide
- Self-retaining gasket

Markets	
---------	--

- |              |            |
|--------------|------------|
| ■ Automation | ■ Robotics |
| ■ Machinery  | ■ Energy   |

Applications
--------------

- Wide net of applications
  - Anywhere existing battleship gray or Eco modular hood/housing applies

Feature	Advantage	Benefit
---------	-----------	---------

■ Has four internal screws to mount either a metal frame or insert

■ Mating compatibility to metal hoods and housings

■ Customer can partially retrofit old designs. i.e. Can mate new plastic Eco B hood with existing metal bulkhead

■ Rear side assembly with click and mate frame

■ Can build cable assemblies in a separate location then panel and then simply integrate in final assembly

■ Improved assembly production flow and throughput

■ Modular production process for thread bushings

■ Less part numbers to accommodate various gauge requirements

■ Volume pricing advantage