



Quality Products. Service Excellence.

Painted Die-Cast "Stomp Box" Enclosures *1590-STOMP Series*

A Selection of Popular Colors & Sizes



Key Features:

- Rugged, diecast aluminum alloy (tough - yet easy to machine), electronic instrument enclosure.
- Factory powder coated to save stomp box manufacturers and experimenters time & money.
- Coated with a smooth gloss polyester powder coat for a lasting finish, even after machining.
- Smooth finish allows for easy adhesion of labels and/or silk screens.
- Colors are matched to standard RAL colors (see table below).
- Lap joint construction provides protection against access of dust and splashing water. Also provides for improved EMI/RFI shielding.
- Unfinished & textured black version is also available & in many other sizes and styles - See "**Die-Cast Aluminum**" and "**Trapezoid & Octagon Die-Cast**"
- Designed to meet IP54. See gasket kit accessory below to meet IP65. IP65 rating also requires water-tight screws.
- Low side wall draft angle (2 degrees or less) for easy P.C. board mounting.

Replacement Hardware

- Replacement screws - nickel plated, 6-32 x 1/2" - **1590MS100** - Package of 100.
- For an even funkier look - order our black replacement screws, 6-32 x 1/2" - **1590MS50BK** - Package of 50

Tamper-Resistant Hardware (Upgrade!)

- Tamper-resistant screws - nickel plated, 6-32 x 1/2" - **1590MS50T** - Package of 50.
- For an even funkier look - order our black replacement screws, 6-32 x 1/2" - **1590MS50TBK** - Package of 50

Photo Features:



Hammond stomp box enclosures come in traditional sizes and shapes and well as unique trapezoid and octagon models.

Rectangular Enclosures

Part Number	Color	RAL Number	Length	Width	Enclosure Depth (Less Lid)	Optional Gasket
1590G2CB	Cobalt Blue	RAL 5013	3.94	1.97	1.06	1590GGASKET
1590G2GR	Green	RAL 6024	3.94	1.97	1.06	1590GGASKET
1590G2LG	Light Gray	RAL 7035	3.94	1.97	1.06	1590GGASKET
1590G2OR	Orange	RAL 2009	3.94	1.97	1.06	1590GGASKET
1590G2PR	Purple	RAL 4008	3.94	1.97	1.06	1590GGASKET
1590G2RD	Red	RAL 3011	3.94	1.97	1.06	1590GGASKET
1590G2YL	Yellow	RAL 1021	3.94	1.97	1.06	1590GGASKET
1590BCB	Cobalt Blue	RAL 5013	4.40	2.38	1.06	1590BGASKET
1590BGR	Green	RAL 6024	4.40	2.38	1.06	1590BGASKET
1590BLG	Light Gray	RAL 7035	4.40	2.38	1.06	1590BGASKET
1590BOR	Orange	RAL 2009	4.40	2.38	1.06	1590BGASKET
1590BPR	Purple	RAL 4008	4.40	2.38	1.06	1590BGASKET
1590BRD	Red	RAL 3011	4.40	2.38	1.06	1590BGASKET
1590BYL	Yellow	RAL 1021	4.40	2.38	1.06	1590BGASKET
1590B2CB	Cobalt Blue	RAL 5013	4.40	2.38	1.32	1590BGASKET
1590B2GR	Green	RAL 6024	4.40	2.38	1.32	1590BGASKET
1590B2LG	Light Gray	RAL 7035	4.40	2.38	1.32	1590BGASKET
1590B2OR	Orange	RAL 2009	4.40	2.38	1.32	1590BGASKET
1590B2PR	Purple	RAL 4008	4.40	2.38	1.32	1590BGASKET
1590B2RD	Red	RAL 3011	4.40	2.38	1.32	1590BGASKET
1590B2YL	Yellow	RAL 1021	4.40	2.38	1.32	1590BGASKET
1590BSCB	Cobalt Blue	RAL 5013	4.40	2.38	1.50	1590BGASKET
1590BSGR	Green	RAL 6024	4.40	2.38	1.50	1590BGASKET
1590BSLG	Light Gray	RAL 7035	4.40	2.38	1.50	1590BGASKET
1590BSOR	Orange	RAL 2009	4.40	2.38	1.50	1590BGASKET

Part Number	Color	RAL Number	Length	Width	Enclosure Depth (Less Lid)	Optional Gasket
1590BSPR	Purple	RAL 4008	4.40	2.38	1.50	1590BGASKET
1590BSRD	Red	RAL 3011	4.40	2.38	1.50	1590BGASKET
1590BSYL	Yellow	RAL 1021	4.40	2.38	1.50	1590BGASKET
1590B3CB	Cobalt Blue	RAL 5013	4.57	3.03	1.32	1590B3GASKET
1590B3GR	Green	RAL 6024	4.57	3.03	1.32	1590B3GASKET
1590B3LG	Light Gray	RAL 7035	4.57	3.03	1.32	1590B3GASKET
1590B3OR	Orange	RAL 2009	4.57	3.03	1.32	1590B3GASKET
1590B3PR	Purple	RAL 4008	4.57	3.03	1.32	1590B3GASKET
1590B3RD	Red	RAL 3011	4.57	3.03	1.32	1590B3GASKET
1590B3YL	Yellow	RAL 1021	4.57	3.03	1.32	1590B3GASKET
1590BBCB	Cobalt Blue	RAL 5013	4.67	3.68	1.18	1590BBGASKET
1590BBGR	Green	RAL 6024	4.67	3.68	1.18	1590BBGASKET
1590BBLG	Light Gray	RAL 7035	4.67	3.68	1.18	1590BBGASKET
1590BBOR	Orange	RAL 2009	4.67	3.68	1.18	1590BBGASKET
1590BBPR	Purple	RAL 4008	4.67	3.68	1.18	1590BBGASKET
1590BBRD	Red	RAL 3011	4.67	3.68	1.18	1590BBGASKET
1590BBYL	Yellow	RAL 1021	4.67	3.68	1.18	1590BBGASKET
1590BB2CB	Cobalt Blue	RAL 5013	4.70	3.70	1.32	1590BBGASKET
1590BB2GR	Green	RAL 6024	4.70	3.70	1.32	1590BBGASKET
1590BB2LG	Light Gray	RAL 7035	4.70	3.70	1.32	1590BBGASKET
1590BB2OR	Orange	RAL 2009	4.70	3.70	1.32	1590BBGASKET
1590BB2PR	Purple	RAL 4008	4.70	3.70	1.32	1590BBGASKET
1590BB2RD	Red	RAL 3011	4.70	3.70	1.32	1590BBGASKET
1590BB2YL	Yellow	RAL 1021	4.70	3.70	1.32	1590BBGASKET
1590BBSCB	Cobalt Blue	RAL 5013	4.70	3.70	1.50	1590BBGASKET
1590BBSGR	Green	RAL 6024	4.70	3.70	1.50	1590BBGASKET
1590BBSLG	Light Gray	RAL 7035	4.70	3.70	1.50	1590BBGASKET
1590BBSOR	Orange	RAL 2009	4.70	3.70	1.50	1590BBGASKET
1590BBSPR	Purple	RAL 4008	4.70	3.70	1.50	1590BBGASKET
1590BBSRD	Red	RAL 3011	4.70	3.70	1.50	1590BBGASKET
1590BBSYL	Yellow	RAL 1021	4.70	3.70	1.50	1590BBGASKET
1590XXCB	Cobalt Blue	RAL 5013	5.72	4.77	1.39	1590XGASKET
1590XXGR	Green	RAL 6024	5.72	4.77	1.39	1590XGASKET
1590XXLG	Light Gray	RAL 7035	5.72	4.77	1.39	1590XGASKET
1590XXOR	Orange	RAL 2009	5.72	4.77	1.39	1590XGASKET
1590XXPR	Purple	RAL 4008	5.72	4.77	1.39	1590XGASKET
1590XXRD	Red	RAL 3011	5.72	4.77	1.39	1590XGASKET
1590XXYL	Yellow	RAL 1021	5.72	4.77	1.39	1590XGASKET

Trapezoidal and Octagonal Enclosures

Part Number	Color	RAL Number	Shape	Length	Width (Small End)	Width (Large End)	Depth (Less Lid)
1590TRPBCB	Cobalt Blue	RAL 5013	Narrow Trapezoid	4.41	2.42	3.11	1.38
1590TRPBGR	Green	RAL 6024	Narrow Trapezoid	4.41	2.42	3.11	1.38
1590TRPBLG	Light Gray	RAL 7035	Narrow Trapezoid	4.41	2.42	3.11	1.38
1590TRPBOR	Orange	RAL 2009	Narrow Trapezoid	4.41	2.42	3.11	1.38
1590TRPBPR	Purple	RAL 4008	Narrow Trapezoid	4.41	2.42	3.11	1.38
1590TRPBRD	Red	RAL 3011	Narrow Trapezoid	4.41	2.42	3.11	1.38
1590TRPBYL	Yellow	RAL 1021	Narrow Trapezoid	4.41	2.42	3.11	1.38
1590TRPCCB	Cobalt Blue	RAL 5013	Wide Trapezoid	3.74	4.79	5.95	1.38
1590TRPCGR	Green	RAL 6024	Wide Trapezoid	3.74	4.79	5.95	1.38
1590TRPCLG	Light Gray	RAL 7035	Wide Trapezoid	3.74	4.79	5.95	1.38
1590TRPCOR	Orange	RAL 2009	Wide Trapezoid	3.74	4.79	5.95	1.38
1590TRPCPR	Purple	RAL 4008	Wide Trapezoid	3.74	4.79	5.95	1.38

Part Number	Color	RAL Number	Shape	Length	Width (Small End)	Width (Large End)	Depth (Less Lid)
1590TRPCRD	Red	RAL 3011	Wide Trapezoid	3.74	4.79	5.95	1.38
1590TRPCYL	Yellow	RAL 1021	Wide Trapezoid	3.74	4.79	5.95	1.38
1590STPCCB	Cobalt Blue	RAL 5013	Octagon	5.23	5.23	5.23	1.38
1590STPCGR	Green	RAL 6024	Octagon	5.23	5.23	5.23	1.38
1590STPCLG	Light Gray	RAL 7035	Octagon	5.23	5.23	5.23	1.38
1590STPCOR	Orange	RAL 2009	Octagon	5.23	5.23	5.23	1.38
1590STPCPR	Purple	RAL 4008	Octagon	5.23	5.23	5.23	1.38
1590STPCRD	Red	RAL 3011	Octagon	5.23	5.23	5.23	1.38
1590STPCYL	Yellow	RAL 1021	Octagon	5.23	5.23	5.23	1.38

Data subject to change without notice

© 2020. Hammond Manufacturing Ltd. All rights reserved.