

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2192640001

Status:

Active

Overview:

Combo Antennas

Description:

Sunshade 5-in-1 (5G/Wi-Fi/GPS) Antenna Lite, 95.00mm x 95.00mm, 1000.00mm Cables with SMA Plug Male Connectors, Adhesive Mounting



Documents:	
3D Model	Application Specification 2192640001-000 (PDF)
Drawing (PDF)	Packaging Specification 2192640001-001 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification 2192640001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Antennas
Series	219264
Component Type	External Antenna
Function	Signal
Overview	Combo Antennas
Product Name	Sunshade 5-in-1 Antenna Lite
Protocol	Cellular, GPS, Wi-Fi
Taxonomy	Antennas
Type	External Antenna
UPC	196823076343
Physical	
Cable Length	1000.00mm
Length	95.00mm
Mounting Style	Adhesive
Net Weight	267.020/g
Packaging Type	PET Bag
Polarization	Linear, RHCP
Radiation Pattern	High Directivity (GPS), Omnidirectional (4G,WiFi)
Thickness	38.00mm
Width	95.00mm

Electrical	
Band#1 F_End (MHz)	1602
Band#1 F_Start (MHz)	1561
Band#2 F_End (MHz)	960
Band#2 F_Start (MHz)	698
Band#3 F_End (MHz)	2690
Band#3 F_Start (MHz)	1710
Band#4 F_End (MHz)	4200
Band#4 F_Start (MHz)	3300
Band#5 F_End (MHz)	5000
Band#5 F_Start (MHz)	4400
Band#6 F_End (MHz)	2500
Band#6 F_Start (MHz)	2400
Band#7 F_End (MHz)	5850
Band#7 F_Start (MHz)	5150
Band#8 F_End (MHz)	7125
Band#8 F_Start (MHz)	5925
Electrical Connectivity	Cable, SMA Plug Male Connector
Peak Gain (dBi)	See Product Specification
Return Loss - S11 (dB)	< -10, < -4, < -5, < -8
Total Efficiency	See Product Specification

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 7(c)-I,6(c)	
REACH SVHC	
Contained Per - D(2022)4187-DC (10 June 2022)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

219264 Series

Mates With

SMA Jack Female Receptacle

Material Info

Reference - Drawing Numbers

Application Specification	2192640001-000
Packaging Specification	2192640001-001
Product Specification	2192640001-001
Sales Drawing	2192640001-000

This document was generated on 01/05/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION