




- 14 Notes:
1. Material: See chart
 2. Material color: See chart
 3. Maximum percent regrind permissible: 25%
 4. Maximum allowable flash to be: 0.25 mm
 5. Maximum allowable mismatch to be: 0.10 mm
 6. A dimension without an inspection report symbol  does not require inspection. It may be controlled on the individual component drawing.
 - a. Total number of inspections required: 14
 - b. Last number used: 14
 - c. Missing symbols: -
 7. Mounting screw size:
 - M4
 - #8 [0.164 in]
 8. Accomodates cable tie series: T18 - T120
 9. Accomodates 3/8in - 3/4in grip tie: GT.375 - GT.75
 10. Tape may be flush or inside the mount edge
 11. Tape may be flush or extend beyond the edge of the mount
 12. Store product in its original packaging between 4°C to 38°C (40°F to 100°F) and 0-95% relative humidity, the optimum storage conditions are 22°C (72°F) and 50% relative humidity out of direct sunlight

Global Part Number	Part Description	Mount			Adhesive Tape		
		Type	Material	Color	Storage Conditions	Adhesive Material	Color
24-1568	WRMB12AHB-PA66HS-BK	WRMB12AHB	PA66HS	Black (BK)	See note 12	241-002-06 acrylic foam tape (recommended for indoor use only)	Black (BK)
	WRMB12AHB-PA66HS-WH	WRMB12AHB	PA66HS	White (WH)			
24-1569	WRMB12A-PA66HS-BK	WRMB12A	PA66HS	Black (BK)	See note 12	241-001-05 Rubber foam tape (recommended for indoor use only)	White (WH)
	WRMB12A-PA66HS-WH	WRMB12A	PA66HS	White (WH)			

01.3

01.3

Revision level		
Drawing	State	Part
01.3	Design Release	-
Changed	Date (YYYY/MM/DD)	
Spangler	2025/07/08	
Approved	Date (YYYY/MM/DD)	
Mann	2025/07/08	

Revision Record	
ECN 312320	

	
All drawing revision are stored in CAD PDM database	

The copyright of this drawing is reserved by HellermannTyton.	
Units	mm

Drawn	Date (YYYY/MM/DD)
Spangler	2025/03/14
Approved	Date (YYYY/MM/DD)
Toll	2025/03/14
HellermannTyton www.HellermannTyton.com	

Title	WireRail with adhesive tape, 12 x 0.75 inches	Scale	1:2
Drawing-No		Global Project Number	24-1568
24-1568-101-CSU		Format	A3
		Sheet	1/1