


GASKET : SILICONE RUBBER

CRIMP TUBE: BRASS
PLATED NICKEL

PACKAGING: BY POLY BAG



MIL-STD-348A, FIG, 301.1	SMA PLUG INTERFACE
MIL-STD-348A, FIG, 301.1	BNC PLUG INTERFACE
SPECIFICATION	DESCRIPTION

73230-5294	48.000±.591	1219.20±15.00
73230-5293	39.370±.591	1000.00±15.00
73230-5292	36.000±.472	914.40±12.00
73230-5291	24.000±.315	609.60±8.00
73230-5290	12.000±.197	304.80±5.00
PART NO.	IN	MM
	DIM A	

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
FA = 0 FE = 0 FE = 0 #####	DIMENSION UNITS	SCALE	CURRENT REV DESC:				molex CA BNC PLUG STR TO SMA PLUG STR WITH RG58 CABLE EWR#14549-A							
	MM/INCH	3:1												
	GENERAL TOLERANCES (UNLESS SPECIFIED)													
	ANGULAR TOL ± 2.0 °						EC NO: 675763 DRWN: WANGR2 2021/06/17 CHK'D: MYLU07 2021/08/30 APPR: LCHEN03 2021/08/30				PRODUCT CUSTOMER DRAWING			
	4 PLACES	±												
3 PLACES	±													
2 PLACES ±		INITIAL REVISION: DRWN: WANGR2 2021/06/17 APPR: LCHEN03 2021/08/30				DOCUMENT NUMBER 732305290		DOC TYPE PSD	DOC PART 000	REVISION A				
1 PLACE ±														
0 PLACES ±														
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER				
				C-SIZE	73230	SEE TABLE 2		GENERAL MARKET		1 OF 1				