

EV CHARGING

SUNON®



SUNON HIGH RELIABILITY 2BALL FANS

KEY BENEFITS



- Up to ~230 CFM, high static pressure
- Wide temp range -10 to 70°C
- 70,000-hour life (2-ball bearing)
- Custom PWM control + FG tach output
- UL Class A, RoHS, IP52/IP56

HIGH AIRFLOW AND
PRESSURE

LONG- LIFE
RELIABILITY

HARSH- ENVIRONMENT
PERFORMANCE

SMART CONTROL
AND MONITORING

EV CHARGING

SUNON®

SUNON HIGH RELIABILITY

2BALL FANS

FAN SPECIFICATIONS



Model	Size (mm)	Voltage (V)	Airflow (cfm)	Static Pressure (inch-H ₂ O)	Noise (dBA)	IP	Speed (rpm)	Bearing
GF80381B1-Q14U-QE9	80×80×38	12	112.2	2.03	67.4	IP68	11,200	2 Ball
PF80381B1-1Q054-S99	80×80×38	12	110	2.08	63.9	--	11,200	2 Ball
PFC0381BX-1Q60U-SC9	120x120x38	12	232.3	1.14	63.5	IP56	6,000	2 Ball
PFC0382BX-1Q48U-SLP	120x120x38	24	233.7	1.16	62.4	IP52	6,000	2 Ball