

# Mini-Fit® Power Products

## Mini-Fit® Product Features

- Current up to 13.0A
- Fully Isolated Terminals
- W-to-W (Wire-to-Wire)
- Operating Temp: -40 to +105°C
- Positive Locking
- W-to-B (Wire-to-Board)
- 4.20mm Pitch
- Polarized and Keyed
- B-to-B (Board-to-Board)
- Options Include:
- Resin Options
- Terminal Options
- Through Hole
- - V2 or V0
- +265°C Reflow Compliant
- Compliant Pin
- Low-Halogen
- High Cycle (Mini-Fit Plus only)
- Glow-Wire Compatible
- Gold or Tin Plating

## Mini-Fit® TPA (Terminal Position Assurance)

### Mini-Fit® BMI (Blind Mate Interface)

2 to 16  
13.0A  
16 to 24  
16 to 24  
Allows misalignment up to 2.5mm  
Compliant pin

