

20.0 to 80.0A Power Connector Portfolio

Powering Reliable Performance

	Photo	Max. Amperage	AWG	Housing Features	Available Configurations
					
Mega-Fit Power Connectors		23.0A	12-22 AWG	Positive Locking	Wire-to-Wire; Wire-to-Board
Super Sabre Connector System		34.0A	10-12 AWG	Positive Latch; Terminal Position Assurance	Wire-to-Wire; Wire-to-Board
MultiCat Power Connectors with Precision-Machined Contact		40.0A	8-18 AWG	2 keying options; 2 color options; CPA	Wire-to-Wire; Wire-to-Board
Mini-Fit Sr. Power Connectors		50.0A	8-16 AWG	Terminal Position Assurance	Wire-to-Wire, Wire-to-Board
EXTreme Ten60Power Connectors		50.0A: W-to-B 50.0A: W-to-P 60.0A: B-to-B	8-16 AWG	Modular; Terminal Position Assurance	Wire-to-Board; Board-to-Board
EXTreme Guardian Power Connector System		80.0A	6-8 AWG	Positive Locking; Terminal Position Assurance	Wire-to-Wire; Wire-to-Board