

HIGH-SPEED NETWORKING SOLUTIONS ➤ BEST-IN-CLASS DATA RATES FOR SEAMLESS CONNECTIVITY

Protocols by Data Rate Performance

Delivering superior bandwidth and signal integrity, Molex High-Speed Networking Cable solutions are designed to operate across multiple systems and automotive protocols.

Protocols	HSAutoLink I	HSAutoLink II	High-Speed FAKRA Mini (HFM)	HSAutoGig
Data Rate	0-2 Gbps	0-13 Gbps	0-20 Gbps (or 15 GHz)	0-25 Gbps+
A2B	✓	✓		
100Base-T1	✓	✓		
USB2.0	✓	✓		
1000Base-T1	✓	✓		
FPD-LINK-II, III, IV		✓	✓	✓
Apix2		✓	✓	✓
GMSL, GMSL2, GMSL3		✓	✓	✓
Apix3			✓	✓
DisplayPort		✓		
USB3.X		✓		
NGAUTO				✓
10GBase-Tx				✓
Multi-Gigabit		✓	✓	✓
MIPI				✓
PCIe 4.0				✓
HDBase-T				✓

HFM licensed by Rosenberger

www.molex.com/highspeednetworking