



Anchor Mounts

Engineered for Maximum Hold in High-Movement Areas

The Anchor Mount is an extra-large, heavy-duty adhesive cable tie mount engineered for applications where mounting points experience significant movement, stress or tension – especially near hinges, doors or corners. Its expanded footprint and high-bond acrylic adhesive deliver exceptional holding strength, while the heat-stabilized PA66 material ensures reliable performance in high-temperature environments.

Designed to simplify installation and reduce component count, the Anchor Mount can replace multiple standard mounts and also offers screw-mounting holes for mechanical fastening when required.

Key Benefits:

- Larger footprint with high-bond acrylic adhesive for superior adhesion strength
- Heat-stabilized PA66 available in black or white for high-heat environments
- Reduces part count – one Anchor Mount can replace up to four standard mounts
- Optional screw-mounting holes provide additional mechanical fastening flexibility

Scan the QR code for more information



Anchor Mount



Part Number	Description	Qty
151-04681	Acrylic Adhesive Anchor Mount, 2.4 x 2.4", Use With T18-T120 Cable Ties or GT.375 Grip Tie, PA66HS, White	50