


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/05/22	GUTTADAURO



TABULATION BLOCK	
ITEM NO.	LENGTH $\pm .6$ [15]
C13LPSCHRA-10-1M	39.4 [1000]
C13LPSCHRA-10-2M	78.7 [2000]

NOTES:

1. PLUG: TYPE CEE7/VII (RIGHT-ANGLED), BLACK
2. CONNECTOR: EN60320 C13 LOCK PLUS, BLACK
3. CORDAGE: H05VVF3G1.0mm², BLACK
- COLOR CODING OF CONDUCTORS: BLUE, BROWN, GREEN/YELLOW
- APPROVALS: VDE, ENEC
- RATING: 10A/250V
4. OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
5. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	L-com™ an INFINITe brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = $+1$ [25] / -0 > 12 [305] ≤ 60 [1524] = $+2$ [51] / -0 > 60 [1524] ≤ 120 [3048] = $+4$ [102] / -0 > 120 [3048] ≤ 300 [7620] = $+6$ [152] / -0 > 300 [7620] = $+5\%$ / -0	DRAWN BY VTHANGARAJ	09/05/22	CATEGORY		
	CHECKED BY DGUST	09/05/22			POWER PRODUCTS
	APPROVED BY GUTTADAURO	09/05/22			PRODUCT DESCRIPTION IEC LOCK C13+ TO R/A SCHUKO, 10A, 250V
ALL OTHER DIMENSIONAL TOLERANCES: $.X = \pm .2$ [5] $.XX = \pm .02$ [5] $.XXX = \pm .005$ [1.3]	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SIZE A	CAGE CODE 43321	ITEM NO. C13LPSCHRA-10	REV. A
FRACTIONS $\pm 1/32$ ANGLES $\pm 1^\circ$	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: C13LPSCHRA-10.SLDDRW	SHEET 1 OF 1	