

**Sherex Fastening Solutions, LLC.**

400 Riverwalk Pkwy, Suite 600

Tonawanda, NY 14150

**Toll Free:** 866.474.3739**Tel:** 716.875.0315**Fax:** 716.875.0358**Email:** [info@sherex.com](mailto:info@sherex.com)

## CFT/CAT Series – Steel (Inches) | Cadmium Free Small Flange 360° Swaging Rivet Nut

### Cadmium Free Small Flange 360° Swaging Series

Actual hole size can be affected by parent material and material thickness. Sherex recommends trial installations to determine the proper grip range for the application. Contact Sherex for details.

#### CFT Series available in different finishes

Use prefix CAT to receive parts with cadmium finish

*Special sizes available upon request.*

Sherex rivet nuts are compatible with the following hardware:

**GRADE 2, GRADE 5, CLASS 8.8, and CLASS 9.8**

Please contact Sherex

+ [more](#)



Item #	Thread Size	HD $\pm$ .005 (inch)	L $\pm$ .015 (inch)	D (Max.) (inches)	3D CAD
<u>CFT2/CAT2-</u> <u>0440</u>	#4-40 UNC	.211	.370	.1875	
<u>CFT2/CAT2-</u> <u>0632</u>	#6-32 UNC	.240	.370	.2185	
<u>CFT2/CAT2-</u> <u>0832</u>	#8-32 UNC	.269	.370	.2495	
<u>CFT2/CAT2-</u> <u>1024</u>	#10-24 UNC	.306	.370	.2805	
<u>CFT2/CAT2-</u> <u>1032</u>	#10-32 UNF	.306	.370	.2805	
<u>CFT2/CAT2-</u> <u>2520</u>	1/4-20 UNC	.400	.515	.3745	
<u>CFT2/CAT2-</u> <u>3118</u>	5/16-18 UNC	.528	.615	.4995	
<u>CFT2/CAT2-</u> <u>3716</u>	3/8-16 UNC	.588	.745	.5615	
<u>CFT2/CAT2-</u> <u>5013</u>	1/2-13 UNC	.800	.935	.7485	