

**Sherex Fastening Solutions, LLC.**

400 Riverwalk Pkwy, Suite 600

Tonawanda, NY 14150

Toll Free: 866.474.3739**Tel:** 716.875.0315**Fax:** 716.875.0358**Email:** info@sherex.com

CFT/CAT Series – Steel (Metric)

Cadmium Free Small Flange 360° Swaging Series

Actual hole size can be affected by parent material and material thickness. Sherex recommends trial installations to determine the proper grip range for the application. Contact Sherex for details.

CFT Series available in different finishes

Use prefix CAT to receive parts with cadmium finish

Special sizes available upon request.







Sherex rivet nuts are compatible with the following hardware:

GRADE 2, GRADE 5, CLASS 8.8, and CLASS 9.8

Please contact Sherex

+ [more](#)



Item #	Thread Size	HD ±.013 (mm)	L ±.38 (mm)	D (Max.) (mm)	3D CAD
<u>CFT2/CAT2-350</u>	M3x0.5 ISO	5.36	9.40	4.76	
<u>CFT2/CAT2-470</u>	M4x0.7 ISO	6.83	9.40	6.34	
<u>CFT2/CAT2-580</u>	M5x0.8 ISO	7.77	9.40	7.12	
<u>CFT2/CAT2-610</u>	M6x1.0 ISO	10.16	13.08	9.51	
<u>CFT2/CAT2-8125</u>	M8x1.25 ISO	13.41	15.62	12.69	
<u>CFT2/CAT2-1015</u>	M10x1.5 ISO	14.94	18.92	14.26	
<u>CFT2/CAT2-12175</u>	M12x1.75 ISO	20.32	23.75	19.01	