

The Industry's' Most Powerful Open-Frame 3x5" Power Supply
NEW Cosel GHA700F
700 Watt High Density Base Plate Cooled AC/DC Power Supply
For Medical and ITE Applications

BF Rated

2 X MOPP

Efficiency up to 95.5%

Leakage Current 0.125/0.250 mA

3X5" 1 U high

Power density of 33.8 Watts/in³



Highest density power supply in a 3" x 5" package with better thermal performance than the very popular Cosel GHA500F.

GHA700F features:

Output Voltages 24, 30, 48, 56 VDC [12 and 65 VDC scheduled to release in Q2 2023]

VTrim: -5% + 10%, 56V output can trim to 61.6V

Medical and industrial safety agency testing

EN61558-2-16, IEC61558-2-16, & EN60601-1 3rd

Operates from -20C to 70C Ambient

400 watts at 70C base plate temp

Remote ON/Off

Aux outputs 5V and 12V both

OVP & OCP Standard

Universal Input 85 to 264 VAC

PFC

5 Year Warranty

Cosel is a leader in quality and technical support, with a Field Failure rate <30 PPM