

Gravity: 4-Digital LED Segment Display Module (Green)

DFR0645-G

Product Overview

06/02/2022

For the most up-to-date information, visit www.mouser.com or the supplier's website.

Description

DFRobot DFR0645-G Gravity: 4-Digital LED Segment Display Module (Green) features an 8-level adjustable brightness and a standard I²C port. This display module is offered in green with an 8 segment x 4 digit display mode. The DFR0645-G display modules offers independent control of the decimal points. Additionally, the DFR0645-G display modules has a 5V DC operating voltage, <55mA operating current, and an operating temperature range of -40°C to 85°C.



Features

- Display mode:
 - 8 segment × 4 digit
- Adjustable brightness
- Supports 8-level brightness adjustment
- I²C communication
- Independent control of decimal points



Features

- 1x 4-Digital LED segment display module (Green)
- 1x Gravity-4Pin I²C connector

Specifications

- 5V DC operating voltage
- <55mA operating current
- -40°C to 85°C operating temperature range
- -55°C to 125°C storage temperature range
- 5.05cm x 1.9cm (2.0" x 0.75") digital tube size
- 6.7cm x 2.2cm (2.64" x 0.87") PCB size

Mouser Part Number

[View Part](#)

To learn more, visit <https://www.mouser.com/new/dfrobot/dfrobot-dfr0645-display-modules/>