


CL05C102JB51PN


Specifications

Property	Nominal Capacitance	Capacitance Tolerance	Rated Vdc	TCC	Size	Length	Width	Thickness
Value	1.0nF	±5%	50.0Vdc	C0G	0402(unit:inch), 1005(unit:mm)	1.00±0.05mm	0.50±0.05mm	0.50±0.05mm


Data Graph




Frequency Characteristics
Network Analyzer




Temperature Characteristics of Capacitance(TCC)
LCR meter, 1000kHz, 1Vrms



DC Bias Characteristics
LCR meter, 1000kHz, 1Vrms



Bias TCC Characteristics
LCR meter, 1000kHz, 1Vrms, 25Vdc



AC Voltage Characteristics
LCR meter, 1000kHz



Any data in this sheet are subject to change, modify or discontinue without notice. The data sheets include the typical data for design reference only. If there is any question regarding the data sheets, please contact our sales personnel or application engineers.