



FEATURES

- * 100W Isolated Output
- * Efficiency to 93%
- * 200KHz Switching Frequency
- * 3:1 Input Range
- * Regulated Outputs
- * Remote On/Off
- * Over Temperature Protection
- * Over Voltage/Current Protection
- * Continuous Short Circuit Protection
- * Quarter Brick Size Meet Industrial Standard
- * CE Mark Meets 2004/108/EC
- * UL60950-1 Approval (Except 3.3 Vout)
- * Meet EN50155

CQB100-110S SERIES

100 WATT

DC-DC CONVERTERS



MODEL NUMBER	INPUT VOLTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT		INPUT CURRENT		% EFF.	CAPACITOR LOAD MAX.
			MIN.	MAX.	NO LOAD	FULL LOAD		
CQB100-110S3V3	66-160 VDC	3.3 VDC	0 mA	25 A	40 mA	833 mA	90	10000μF
CQB100-110S05	66-160 VDC	5.0 VDC	0 mA	20 A	30 mA	983 mA	92.5	10000μF
CQB100-110S12	66-160 VDC	12 VDC	0 mA	8.4 A	40 mA	985 mA	93	8800μF
CQB100-110S24	66-160 VDC	24 VDC	0 mA	4.2 A	60 mA	996 mA	92	1500μF

NOTE: 1. Nominal Input Voltage 110VDC

