

Distribution Box



Part No.	Dimensions (WxLxD)	Anti-collision Level	IP Level	Gland Plate	Lock Q'ty	Safety
ST202015	200x200x150mm	IK10	66	ax1	1	
ST203015	200x300x150mm	IK10	66	ax1	1	
ST253015	250x300x150mm	IK10	66	ax1	1	
ST253020	250x300x200mm	IK10	66	ax1	1	
ST303015	300x300x150mm	IK10	66	bx1	1	
ST303020	300x300x200mm	IK10	66	bx1	1	
ST304015	300x400x150mm	IK10	66	bx1	1	
ST304020	300x400x200mm	IK10	66	bx1	1	
ST305015	300x500x150mm	IK10	66	bx1	1	
ST305020	300x500x200mm	IK10	66	bx1	1	
ST403015	400x300x150mm	IK10	66	bx1	1	
ST403020	400x300x200mm	IK10	66	cx1	1	
ST404020	400x400x200mm	IK10	66	cx1	1	
ST405015	400x500x150mm	IK10	66	bx1	1	
ST405020	400x500x200mm	IK10	66	cx1	1	
ST405025	400x500x250mm	IK10	66	cx1	1	
ST406020	400x600x200mm	IK10	66	cx1	2	
ST406025	400x600x250mm	IK10	66	cx1	2	
ST406030	400x600x300mm	IK10	66	cx1	2	
ST505020	500x500x200mm	IK10	66	dx1	1	
ST505025	500x500x250mm	IK10	66	dx1	1	
ST506020	500x600x200mm	IK10	66	dx1	2	
ST506025	500x600x250mm	IK10	66	dx1	2	
ST507020	500x700x200mm	IK10	66	dx1	2	
ST507025	500x700x250mm	IK10	66	dx1	2	

CE

Part No.	Dimensions (WxLxD)	Anti-collision Level	IP Level	Gland Plate	Lock Q'ty	Safety
ST604020	600x400x200mm	IK10	66	dx1	1	CE
ST604025	600x400x250mm	IK10	66	dx1	1	
ST604030	600x400x300mm	IK10	66	dx1	1	
ST606020	600x600x200mm	IK10	66	dx1	2	
ST606025	600x600x200mm	IK10	66	dx1	2	
ST606030	600x600x300mm	IK10	66	dx1	2	
ST606040	600x600x400mm	IK10	66	dx1	2	
ST608020	600x800x200mm	IK10	66	dx1	2	
ST608025	600x800x250mm	IK10	66	dx1	2	
ST608030	600x800x300mm	IK10	66	dx1	2	
ST6010020	600x1000x200mm	IK10	66	dx1	3	
ST6010025	600x1000x250mm	IK10	66	dx1	3	
ST6010030	600x1000x300mm	IK10	66	dx1	3	
ST6010040	600x1000x400mm	IK10	66	dx1	3	
ST6012020	600x1200x200mm	IK10	66	dx1	3	
ST6012030	600x1200x300mm	IK10	66	dx1	3	
ST6012040	600x1200x400mm	IK10	66	dx1	3	
ST705020	700x500x200mm	IK10	66	dx1	1	
ST705025	700x500x250mm	IK10	66	dx1	1	
ST808025	800x800x250mm	IK10	66	cx2	2	
ST808030	800x800x300mm	IK10	66	cx2	2	
ST8010025	800x1000x250mm	IK10	66	cx2	3	
ST8010030	800x1000x300mm	IK10	66	cx2	3	
ST8012030	800x1200x300mm	IK10	66	cx2	3	