


Height 1.15mm

Push-Push, Ultra Low Profile, micro SD™ Card Connector



## Features


- 1 Ultra Low profile 1.15mm height
- 2 Prevents incorrect card insertion
- 3 Excellent card lock mechanism
- 4 Prevents mis card insertion
- 5 Card detection switch (Normally close)




The world's  
lowest profile  
in its Class  
1.15 mm\*

\* As push-push type  
micro SD™ connector  
as of June 2016

## Dimensions



## Prevents card jamming if nano SIM inserted



Easy to remove the card  
when accidentally inserted

## Specifications

Contact Resistance	60mΩ Max. (Signal) 200mΩ Max. (Detection)
Withstanding Voltage	500V AC for 1 minute
Mold Resistance	1,000MΩ Min. (500V DC)
Rated Current	0.5A
Rated Voltage	10V AC
Operating Temperature	-30°C to +85°C
Mating cycles	10,000 times

- RoHS compliant, Halogen-free product\*

\*This product satisfies halogen free requirements defined as 900ppm maximum chlorine, 900ppm maximum bromine, and 1500ppm maximum total of chlorine and bromine

※ Please contact Hirose's sales representative prior to adopting the products to in-vehicle devices.