

MODBUS RTU/TCP DISPLAY WITH TOUCH PANEL

EA HMI SERIES



FEATURES

- Brilliant color display with typ. 1,000 cd/m²
- Touch panel included
- Wide viewing angle with $\pm 170^\circ$
- Modbus RTU and TCP
- Free definable display content: text, pictures, value, bargraph, instrument...
- Supports up to 256 modbus register
- Many interface options, RS485, LAN, WiFi, Modbus....
- Wide power supply range 5V..30V=
- Wall mount and panel mount
- More sizes are under development
- Quick and easy cable commissioning thanks to tool-free push-in connection technology

ORDERING CODE



Small/Short
Protocol

4.3" Touch, WiFi and RS485 **EA HMI043WU-42ATCS**

4.3" Touch, LAN, WiFi and RS485 **EA HMI043LU-42ATCS**



4.3" Touch, Modbus RTU/TCP, WiFi
and RS485 **EA HMI043WM-42ATCS**

4.3" Touch, Modbus RTU/TCP, LAN,
WiFi and RS485 **EA HMI043LM-42ATCS**

ACCESSORIES

Mounting clips (2 pcs.)	EA 00C1-1KNS
24V= power supply unit 110/230V~	EA PS24V-18W
Y cable for power supply (for 1-2 displays)	EA KH21-102Y
USB <-> RS-485 Adaptor	EA 9790-USB485