

Gold Option	Gold Mouser Part Number	Cost-Optimized Alternative	Cost-Optimized Alternative Mouser Part Number
ERM8-010-05.0-S-DV-K-TR	200-ERM8010050SDVKTR	ERM8-010-05.0-L-DV-K-TR	200-ERM8010050LDVKTR
ERM8-010-05.0-S-DV-L-K-TR	200-ERM801005.0SDVLK	ERM8-010-05.0-L-DV-L-K-TR	200-ERM801005.0LDVLK
ERM8-010-05.0-S-DV-L-TR	200-ERM8010050SDVLTR	ERM8-010-05.0-L-DV-L-TR	200-ERM8010050LDVLTR
ERM8-010-09.0-S-DV-K-TR	200-ERM8010090SDVKTR	ERM8-010-09.0-L-DV-K-TR	200-ERM8010090LDVKTR
ERM8-010-09.0-S-DV-TR	200-ERM8010090SDVTR	ERM8-010-09.0-L-DV-TR	200-ERM801009.0LDVTR
ERM8-013-05.0-S-DV-DS-L-K-TR	200-8013050SDVDSLKTR	ERM8-013-05.0-L-DV-DS-L-K-TR	200-8013050LDVDSLKTR
ERM8-013-05.0-S-DV-K-TR	200-ERM8013050SDVKTR	ERM8-013-05.0-L-DV-K-TR	200-ERM8013050LDVKTR
ERM8-013-05.0-S-DV-L-K-TR	200-ERM801305.0SDVLK	ERM8-013-05.0-L-DV-L-K-TR	200-ERM801305.0LDVLK
ERM8-013-09.0-S-DV-K-TR	200-ERM8013090SDVKTR	ERM8-013-09.0-L-DV-K-TR	200-ERM8013090LDVKTR
ERM8-020-02.0-S-DV-P-FR	200-ERM8020020SDVPFR	ERM8-020-02.0-L-DV-P-FR	200-ERM802002.0LDVP
ERM8-020-02.0-S-DV-P-TR	200-ERM8-2002SDVPTR	ERM8-020-02.0-L-DV-P-TR	200-ERM80202.0LDVPTR
ERM8-020-02.0-S-DV-TR	200-ERM802002.0SDVTR	ERM8-020-02.0-L-DV-TR	200-ERM802002.0LDVTR
ERM8-020-05.0-S-DV-K-TR	200-ERM8020050SDVKTR	ERM8-020-05.0-L-DV-K-TR	200-ERM8020050LDVKTR
ERM8-020-05.0-S-DV-L-K-TR	200-ERM802005.0SDVLK	ERM8-020-05.0-L-DV-L-K-TR	200-ERM802005.0LDVLK
ERM8-020-05.0-S-DV-L-TR	200-ERM8020050SDVLTR	ERM8-020-05.0-L-DV-L-TR	200-ERM8020050LDVLTR
ERM8-020-05.0-S-DV-TR	200-ERM802005.0SDVTR	ERM8-020-05.0-L-DV-TR	200-ERM802005.0LDVTR
ERM8-020-08.0-S-DV-K-TR	200-ERM8020080SDVKTR	ERM8-020-08.0-L-DV-K-TR	200-ERM8020080LDVKTR
ERM8-020-09.0-S-DV-K-FR	200-ERM8020090SDVKFR	ERM8-020-09.0-L-DV-K-FR	200-ERM8020090LDKR
ERM8-020-09.0-S-DV-K-TR	200-ERM8020090SDVKTR	ERM8-020-09.0-L-DV-K-TR	200-ERM8020090LDVKTR
ERM8-025-02.0-S-DV-P-TR	200-ERM8-02502SDVPTR	ERM8-025-02.0-L-DV-P-TR	200-ERM8-02502LDVPTR
ERM8-025-02.0-S-DV-TR	200-ERM802502.0SDVTR	ERM8-025-02.0-L-DV-TR	200-ERM802502.0LDVTR
ERM8-025-05.0-S-DV-K-TR	200-ERM8025050SDVKTR	ERM8-025-05.0-L-DV-K-TR	200-ERM8025050LDVKTR
ERM8-025-05.0-S-DV-L-K-TR	200-ERM802505.0SDVLK	ERM8-025-05.0-L-DV-L-K-TR	200-ERM802505.0LDVLK
ERM8-025-05.0-S-DV-L-TR	200-ERM8025050SDVLTR	ERM8-025-05.0-L-DV-L-TR	200-ERM8025050LDVLTR
ERM8-025-05.0-S-DV-TR	200-ERM802505.0SDVTR	ERM8-025-05.0-L-DV-TR	200-ERM802505.0LDVTR
ERM8-025-08.0-S-DV-K-TR	200-ERM8025080SDVKTR	ERM8-025-08.0-L-DV-K-TR	200-ERM8025080LDVKTR
ERM8-025-09.0-S-DV-K-TR	200-ERM8025090SDVKTR	ERM8-025-09.0-L-DV-K-TR	200-ERM8025090LDVKTR

Gold Option	Gold Mouser Part Number	Cost-Optimized Alternative	Cost-Optimized Alternative Mouser Part Number
ERM8-025-09.0-S-DV-TR	200-ERM8025090SDVTR	ERM8-025-09.0-L-DV-TR	200-ERM802509.0LDVTR
ERM8-030-01-S-D-RA-K-TR	200-ERM803001SDRAKTR	ERM8-030-01-L-D-RA-K-TR	200-ERM803001LDRAKTR
ERM8-030-02.0-S-DV-P-TR	200-ERM8-3002SDVPTR	ERM8-030-02.0-L-DV-P-TR	200-ERM8-3002LDVPTR
ERM8-030-02.0-S-DV-TR	200-ERM803002.0SDVTR	ERM8-030-02.0-L-DV-TR	200-ERM803002.0LDVTR
ERM8-030-05.0-S-DV-K-FR	200-ERM8030050SDVKFR	ERM8-030-05.0-L-DV-K-FR	200-ERM8030050LDVKFR
ERM8-030-05.0-S-DV-K-TR	200-ERM8030050SDVKTR	ERM8-030-05.0-L-DV-K-TR	200-ERM8030050LDVKTR
ERM8-030-05.0-S-DV-L-K-FR	200-ERM8030050SDVLKFE	ERM8-030-05.0-L-DV-L-K-FR	200-ERM8030050LDVLKFE
ERM8-030-05.0-S-DV-L-K-TR	200-ERM803005.0SDVLK	ERM8-030-05.0-L-DV-L-K-TR	200-ERM803005.0LDVLK
ERM8-030-05.0-S-DV-L-TR	200-ERM8030050SDVLTR	ERM8-030-05.0-L-DV-L-TR	200-ERM8030050LDVLTR
ERM8-030-08.0-S-DV-K-TR	200-ERM8030080SDVKTR	ERM8-030-08.0-L-DV-K-TR	200-ERM8030080LDVKTR
ERM8-030-09.0-S-DV-K-FR	200-ERM8030090SDVKFR	ERM8-030-09.0-L-DV-K-FR	200-ERM8030090LDVKFR
ERM8-030-09.0-S-DV-K-TR	200-ERM8030090SDVKTR	ERM8-030-09.0-L-DV-K-TR	200-ERM8030090LDVKTR
ERM8-030-09.0-S-DV-S-K-TR	200-RM8030090SDVSKTR	ERM8-030-09.0-L-DV-L-K-TR	200-RM8030090LDVSKTR
ERM8-035-05.0-S-DV-K-TR	200-ERM8035050SDVKTR	ERM8-035-05.0-L-DV-K-TR	200-ERM8035050LDVKTR
ERM8-040-02.0-S-DV-P-TR	200-ERM8-4002SDVPTR	ERM8-040-02.0-L-DV-P-TR	200-ERM8-4002LDVPTR
ERM8-040-02.0-S-DV-TR	200-ERM804002.0SDVTR	ERM8-040-02.0-L-DV-TR	200-ERM804002.0LDVTR
ERM8-040-05.0-S-DV-EGP-K-TR	200-8040050SDVEGPKTR	ERM8-040-05.0-L-DV-EGP-K-TR	200-8040050LDVEGPKTR
ERM8-040-05.0-S-DV-K-TR	200-ERM8040050SDVKTR	ERM8-040-05.0-L-DV-K-TR	200-ERM8040050LDVKTR
ERM8-040-05.0-S-DV-L-K-TR	200-ERM804005.0SDVLK	ERM8-040-05.0-L-DV-L-K-TR	200-ERM804005.0LDVLK
ERM8-040-05.0-S-DV-L-TR	200-ERM8040050SDVLTR	ERM8-040-05.0-L-DV-L-TR	200-ERM8040050LDVLTR
ERM8-040-05.0-S-DV-TR	200-ERM804005.0SDVTR	ERM8-040-05.0-L-DV-TR	200-ERM804005.0LDVTR
ERM8-040-08.0-S-DV-K-TR	200-ERM8040080SDVKTR	ERM8-040-08.0-L-DV-K-TR	200-ERM8040080LDVKTR
ERM8-040-09.0-S-DV-K-TR	200-ERM8040090SDVKTR	ERM8-040-09.0-L-DV-K-TR	200-ERM8040090LDVKTR
ERM8-049-05.0-S-DV-DS-L-K-TR	200-8049050SDVDSLKTR	ERM8-049-05.0-L-DV-DS-L-K-TR	200-8049050LDVDSLKTR
ERM8-050-01-S-D-RA-K-TR	200-ERM805001SDRAKTR	ERM8-050-01-L-D-RA-K-TR	200-ERM805001LDRAKTR
ERM8-050-01-S-D-RA-L-K-TR	200-ERM80501SDRALKTR	ERM8-050-01-L-D-RA-L-K-TR	200-ERM80501LDRALKTR
ERM8-050-02.0-S-DV-TR	200-ERM805002.0SDVTR	ERM8-050-02.0-L-DV-TR	200-ERM805002.0LDVTR
ERM8-050-05.0-S-DV-EGP-TR	200-ERM805005SDVEGP	ERM8-050-05.0-L-DV-EGP-TR	200-M8050050LDVEGPTR
ERM8-050-05.0-S-DV-K-TR	200-ERM8050050SDVKTR	ERM8-050-05.0-L-DV-K-TR	200-ERM8050050LDVKTR
ERM8-050-05.0-S-DV-L-K-TR	200-ERM855SDVLKTR	ERM8-050-05.0-L-DV-L-K-TR	200-ERM805005.0LDVLK
ERM8-050-05.0-S-DV-L-TR	200-ERM8050050SDVLTR	ERM8-050-05.0-L-DV-L-TR	200-ERM8050050LDVLTR

Gold Option	Gold Mouser Part Number	Cost-Optimized Alternative	Cost-Optimized Alternative Mouser Part Number
ERM8-050-09.0-S-DV-K-TR	200-ERM8050090SDVKTR	ERM8-050-09.0-L-DV-K-TR	200-ERM8050090LDVKTR
ERM8-060-01-S-D-RA-TR	200-ERM806001SDRATR	ERM8-060-01-L-D-RA-TR	200-ERM806001LDRATR
ERM8-060-02.0-S-DV-P-TR	200-ERM8-06002SDVPTR	ERM8-060-02.0-L-DV-P-TR	200-ERM8-06002LDVPTR
ERM8-060-05.0-S-DV-K-FR	200-ERM8060050SDVKFR	ERM8-060-05.0-L-DV-K-FR	200-ERM8060050LDVKFR
ERM8-060-05.0-S-DV-K-TR	200-ERM8060050SDVKTR	ERM8-060-05.0-L-DV-K-TR	200-ERM8060050LDVKTR
ERM8-060-05.0-S-DV-L-K-TR	200-ERM80605SDVLKTR	ERM8-060-05.0-L-DV-L-K-TR	200-ERM806005.0LDVLK
ERM8-060-05.0-S-DV-TR	200-ERM806005.0SDVTR	ERM8-060-05.0-L-DV-TR	200-ERM806005.0LDVTR
ERM8-070-03-S-D-RA-K-TR	200-ERM807003SDRAKTR	ERM8-070-03-L-D-RA-K-TR	200-ERM807003LDRAKTR
ERM8-070-05.0-S-DV-EGP-K-TR	200-8070050SDVEGPKTR	ERM8-070-05.0-L-DV-EGP-K-TR	200-8070050LDVEGPKTR
ERM8-070-05.0-S-DV-L-K-TR	200-ERM80705SDVLKTR	ERM8-070-05.0-L-DV-L-K-TR	200-ERM80705LDVLKTR
ERM8-070-05.0-S-DV-L-TR	200-ERM8070050SDVLTR	ERM8-070-05.0-L-DV-L-TR	200-ERM8070050LDVLTR
ERM8-075-01-S-D-RA-L-K-TR	200-ERM80751SDRALKTR	ERM8-075-01-L-D-RA-L-K-TR	200-ERM87501LDRALKTR
ERM8-075-02.0-S-DV-P-TR	200-ERM8-07502SDVPTR	ERM8-075-02.0-L-DV-P-TR	200-ERM8-07502LDVPTR
ERM8-075-05.0-S-DV-K-TR	200-ERM8075050SDVKTR	ERM8-075-05.0-L-DV-K-TR	200-ERM8075050LDVKTR
ERM8-075-05.0-S-DV-L-K-TR	200-ERM80755SDVLKTR	ERM8-075-05.0-L-DV-L-K-TR	200-ERM80755LDVLKTR
ERM8-075-05.0-S-DV-L-TR	200-ERM8075050SDVLTR	ERM8-075-05.0-L-DV-L-TR	200-ERM8075050LDVLTR
ERM8-075-09.0-S-DV-K-TR	200-ERM8075090SDVKTR	ERM8-075-09.0-L-DV-K-TR	200-ERM8075090LDVKTR
ERM8-075-09.0-S-DV-TR	200-ERM8075090SDVTR	ERM8-075-09.0-L-DV-TR	200-ERM807509.0LDVTR
ERM8-100-09.0-S-DV-K	200-ERM8100090SDVK	ERM8-100-09.0-L-DV-K	200-ERM8100090LDVK