




Features

- Onboard Intel® Atom™ x7-E3950, 2.0GHz or x5-E3940 1.8GHz or x5-E3930, 1.8GHz [i-Temp support]
- Onboard DDR3L memory
- 1x Intel® I210IT PCI-E Gigabit LAN
- Supports TPM (2.0), eMMC5.0 (optional)
- Wide-range operating temperature

Specifications

CPU	Intel® Atom™ QC x7/ E3950 (1.6GHz~2.0GHz) Intel® Atom™ QC x5/ E3940 (1.6 GHz~1.8GHz) Intel® Atom™ DC x5/ E3930 (1.3 GHz~1.8GHz) Intel® Pentium® QC N4200 (1.10GHz~ 2.50GHz) Intel® Celeron® DC N3350 (1.10GHz~ 2.40GHz)
PCH	Integrated in Intel® SoC
Memory Type	Onboard memory, DDR3L 1600MHz, 4GB with ECC
BIOS	AMI
Watchdog Timer	256 levels
H/W Monitor	Yes
Storage Device Interface	eMMC 5.0 up to 32GB (optional)
Expansion slots	4x PCI-E(x1)
Graphics Controller	Intel® SoC integrated Gen9-LP graphics
Video Output	1x DDI 1x LVDS or 1x eDP (optional)
Ethernet	Intel® I210IT PCI-E Gigabit LAN
I/O Chip	Fintek F81804U-I
Serial Port	2x UART (Tx/Rx only))
USB 2.0	8x USB 2.0 via Carrier Board
USB 3.0/ 3.1	2x USB 3.0 via Carrier Board
Serial ATA	2x SATA III via Carrier Board
Audio	Intel® Atom™ SoC built-in HD audio controller
TPM	TPM (2.0)
Others	I2C
Dimensions (L X W)	84mm x 55mm (3.3" x 2.17")
Power Consumption	TBD
Operating Temperature	-20°C ~ 60°C (-4°F~176°F)(ET876-420/ET876-335) -40°C ~ 85°C (-40°F~185°F)(ET876-x7/x5)
Storage Temperature	-40°C ~ 90°C (-40°F ~ 194°F)
Relative Humidity	90% (non-condensing @60°C)

Ordering Information

ET876-X7LV	COM Express (Type 10) CPU Module with Intel® Atom™ x7/ E3950 (2.0GHz) on board, LVDS, 4GB DDR3L memory on board
ET876-X5QLV	COM Express (Type 10) CPU Module with Intel® Atom™ x5/ E3940 (1.8GHz) on board, LVDS, 4GB DDR3L memory on board
ET876-X5LV	COM Express (Type 10) CPU Module with Intel® Atom™ x5/ E3930 (1.8GHz) on board, LVDS, 4GB DDR3L memory on board
ET876-420LV	COM Express (Type 10) CPU Module with Intel® Pentium® N4200 (2.5GHz) on board, LVDS, 4GB DDR3L memory on board
ET876-335LV	COM Express (Type 10) CPU Module with Intel® Celeron® N3350 (2.4GHz) on board, LVDS, 4GB DDR3L memory on board
IP417	Mini-ITX COM Express Type 10 (R3.0) Carrier Board

Dimensions and Drawing

