





Features

- Onboard AMD Ryzen™ Embedded V1000 Series
- Onboard DDR4 memory, Max. 8GB
- 3x independent displays, HDMI/DVI/DisplayPort & LVDS or eDP via carrier board
- 4x USB 3.1, 8x USB 2.0, 2x SATA III
- Supports TPM (2.0)



Specifications

CPU	Onboard AMD Ryzen™ Embedded V1000 Series
PCH	N/A
Memory Type	Onboard Memory, DDR4, Max. 8GB
BIOS	AMI
Watchdog Timer	256 levels
H/W Monitor	Yes
Storage Device Interface	N/A
Expansion Slots	1x PEG(x8) 8x PCI-E(x1)
Graphics Controller	AMD Radeon™ Vega GPU integrated
Video Output	2x DDI 1x LVDS or 1x eDP (option)
Ethernet	Intel® I210IT PCI-E Gigabit LAN
I/O Chip	Fintek F81804U-I
Serial Port	2x UART (Tx/Rx only)
USB 2.0	8x USB 2.0 via carrier board
USB 3.0/ 3.1	4x USB 3.1 via carrier board
Serial ATA	2x SATA III via carrier board
Audio	AMD Ryzen™ built-in HD audio controller
TPM	TPM (2.0)
Others	Digital I/O (4in/4-out)
Dimensions (L X W)	125mm x 95mm (4.92" x 3.74")
Power Consumption	AMD V1807B, 3.35GHz w/ 4GB DDR4-2666 +12V: 6.28A; +5V: 0.28A, +5VSB: 0.16A, +3.3V: 0.52A
Operating Temperature	0°C~60°C (32°F~140°F)
Storage Temperature	-20°C~80°C (-4°F~176°F)
Relative Humidity	90% (non-condensing @60°C)

Ordering Information

ET976-1605LV-G	COM Express (Type-6) CPU Module with AMD Ryzen™ V1605B QC APU (3.6GHz), LVDS, 8GB DDR4 memory on board
ET976-1605LV-4G	COM Express (Type-6) CPU Module with AMD Ryzen™ V1605B QC APU (3.6GHz), LVDS, 4GB DDR4 memory on board
ET976-1605-8G	COM Express (Type-6) CPU Module with AMD Ryzen™ V1605B QC APU (3.6GHz), 8GB DDR4 memory on board
ET976-1605-4G	COM Express (Type-6) CPU Module with AMD Ryzen™ V1605B QC APU (3.6GHz), 4GB DDR4 memory on board
ET976-1202LV-E4G	COM Express (Type-6) CPU Module with AMD Ryzen™ V1202B DC APU (3.2GHz), LVDS, 4GB DDR4 memory on board with ECC
ET976-1202LV-4G	COM Express (Type-6) CPU Module with AMD Ryzen™ V1202B DC APU (3.2GHz), LVDS, 4GB DDR4 memory on board
HESET976-A	Heatsink with Fan for ET976
HSET976-1	Heat spreader for ET976

Dimensions and Drawing

