



Sherex Fastening Solutions, LLC.

400 Riverwalk Pkwy, Suite 600

Tonawanda, NY 14150

Toll Free: 866.474.3739

Tel: 716.875.0315

Fax: 716.875.0358

Email: info@sherex.com

FLEX-5S

Pull to Stroke Installation Tool

The **SFS FLEX-5S** features 7mm of available stroke and is capable of installing rivet nuts from M3 to M10 and 6-32 to 3/8-24 and is based on an innovative modular design. The **FLEX-5S** comes as a pull to stroke tool but offers the flexibility of a pull to pressure installation with Sherex's conversion kit, allowing for the proper method to be used based on the application requirements. The **FLEX-5S** tool has the ability to be upgraded from the original base tool to different levels of process [+ more](#)



1

Item #	Installation Method	Thread Size	Available Stroke	Weight	Complete Head Set Assembly P/N	Mandrel P/N
FLEX-5S 0440	Pull to Stroke	#4-40 UNC	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-0440	M-0440- 200
FLEX-5S 0632	Pull to Stroke	#6-32 UNC	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-0632	M-0632- 200

Item #	Installation Method	Thread Size	Available Stroke	Weight	Complete Head Set Assembly P/N	Mandrel P/N
<u>FLEX-5S 0832</u>	Pull to Stroke	#8-32 UNC	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-0832	M-0832-175
<u>FLEX-5S 1024</u>	Pull to Stroke	#10-24 UNC	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-1024	M-1024-250
<u>FLEX-5S 1032</u>	Pull to Stroke	#10-32 UNF	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-1032	M-1032-250
<u>FLEX-5S 2520</u>	Pull to Stroke	1/4-20 UNC	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-2520	M-2520-250
<u>FLEX-5S 2528</u>	Pull to Stroke	1/4-28 UNF	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-2528	M-2528-250
<u>FLEX-5S 3118</u>	Pull to Stroke	5/16-18 UNC	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-3118	M-3118-250
<u>FLEX-5S 3124</u>	Pull to Stroke	5/16-24 UNF	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-3124	M-3124-250
<u>FLEX-5S 3716</u>	Pull to Stroke	3/8-16 UNC	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-3716	M-3716-250
<u>FLEX-5S 3724</u>	Pull to Stroke	3/8-24 UNF	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-3724	M-3724-250
<u>FLEX-5S M3</u>	Pull to Stroke	M3x0.5 ISO	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-M3	M-M3-45
<u>FLEX-5S M4</u>	Pull to Stroke	M4x0.7 ISO	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-M4	M-M4-45
<u>FLEX-5S M5</u>	Pull to Stroke	M5x0.8 ISO	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-M5	M-M5-65
<u>FLEX-5S M6</u>	Pull to Stroke	M6x1.0 ISO	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-M6	M-M6-65

Item #	Installation Method	Thread Size	Available Stroke	Weight	Complete Head Set Assembly P/N	Mandrel P/N
<u>FLEX-5S M8</u>	Pull to Stroke	M8x1.25 ISO	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-M8	M-M8-65
<u>FLEX-5S M10</u>	Pull to Stroke	M10x1.5 ISO	7 mm (0.276 in)	4.2 lbs. (1.9 kg)	FL5-HS-M10	M-M10-65