



Pushing Performance
Since 1945

Han® 3A Solutions

Rugged and Compact Connectivity

For further information, please reach out to
techsupportUS@HARTING.com

Insert Range

Various insert options ranging from 100A to High-Speed Data Connectivity
Options in wire termination – crimp, screw, QuickLock®, axial screw and IDC

100A
Single Pole



40A
3+GND



16A
5+GND



10A
12+GND



6.5A
21



10G
Ethernet



Fiber
Optics



Hood & Housing Configurations

Many mounting possibilities for any application



Housing Range

Bulkhead Mount, Screw Mount, Inline, Angled, Panel Feed Through

Hood Range

Top Entry, Side Entry

Environmental Protection

Wide selection of hood & housing materials for various degrees of protection



Grey
Metal



HMC
High Mating
Cycle
>10,000 Cycles



Plastic



Marine
For outdoor use



EMC
For higher EMC
requirements



HPR
IP68/69k
For the most
rugged environments



INOX
Stainless Steel



Class 1
Division 2