



Heyco Solar Products Warranty

Heyco manufactures and sells products of the highest quality and stands behind them. In light of those facts, Heyco sells its products with the understanding and on the condition that the purchaser will test them in actual use and make his own determination as to their suitability and acceptability for his intended use, and the purchaser agrees to such condition. Use of Heyco products other than for the applications or environments illustrated herein constitutes a misuse for which the purchaser bears all responsibility.

Heyco warrants to the original purchaser that for a period of twenty (20) years from date of purchase the Heyco solar products shall be free from defects in material and workmanship. Except as set forth in the prior sentence, Heyco makes no other warranty, express or implied, and all other warranties are expressly disclaimed by Heyco. Heyco's obligation under this warranty and that of the seller is limited to the replacement of the defective product or the provision of new components at no charge. Under no circumstances are Heyco or the seller liable for any consequential, special, indirect, incidental, punitive or exemplary losses, damages or expenses, or for lost profits, lost business, or for lost opportunities, arising out of the use and/or inability to use the Heyco solar products, regardless of whether Heyco has been advised of the possibility of such damages.

In order to qualify for this warranty, the original purchaser must have installed the Heyco solar products in accordance with the appropriate Heyco installation instructions and all commercial building wiring standards and must not have subjected the Heyco solar products to abuse or mishandling.

Force Majeure – Heyco shall not be responsible or liable in any way to the purchaser for any failure or delay in performance under this warranty due to any cause beyond its control such as war, riots, strikes, natural disaster, acts of God, acts of terrorism, flood, fire, accident, delay in transportation, intervention by governmental entities, change in laws or regulations or any other unforeseen event beyond its control.

Heyco Solar Products Warranty – Parts List (as of 1/19/2021)

PART	DESCRIPTION
S3328	CC H 1/2 SS COATED
S3378	CC H 1/2 STAINLESS
S3324	CC H 1/4 SS COATED
S3374	CC H 1/4 STAINLESS
S3332	CC H 3/4 SS COATED
S3382	CC H 3/4 STAINLESS
S3326	CC H 3/8 SS COATED
S3376	CC H 3/8 STAINLESS
S3330	CC H 5/8 SS COATED
S3380	CC H 5/8 STAINLESS
S3334	CC H 7/8 SS COATED
S3384	CC H 7/8 STAINLESS
S6520	HELIOS UVX CLIP 100/BAG
S6560	HELIOS UVX CLIP BULK
S6526	LC 14-4 1-POLE CU
S6525	LC 14-4 1-POLE CU TINNED
M8437GBF	LTCG 1 BLK 9-4.5MM W/2252
M8437GAL	LTCG 1 NPT BLK 6-6.5MM N/N
M3231GAE	LTCG 1/2 BLK 2-5.2MM W/2250U
M4524GBG	LTCG 1-1/4 BLK 13-4.5MM W/9806
M4524GAL	LTCG 1-1/4 NPT BLK 6-6.5MM N/N
M3234GAF	LTCG 3/4 BLK 3-5.2MM W/2251
M3234GAG	LTCG 3/4 BLK 4-5.2MM W/2251
M3234GAN	LTCG 3/4 NPT BLK 2-7.4MM N/N
M3234GAM	LTCG 3/4 NPT BLK 3-7.0MM N/N
M3234GBC	LTCG 3/4 NPT BLK 4-6.0MM N/N
M3200GAH	LTCG LL1/2 BLK 3-5.6MM W/2250U
M3200GAJ	LTCG LL1/2 NPT BLK 2-6.0MM N/N
S6403	MAXRUNNER 12 CLIP
S6433	MAXRUNNER 12 FLUSH MOUNT
S6530	MSS 14-2 1-POLE
S6540	NB 14-4 10-POLE
S6541	NB 14-4 12-POLE
S6535	NB 14-4 2-POLE
S6536	NB 14-4 3-POLE
S6537	NB 14-4 5-POLE
S6538	NB 14-4 6-POLE

S6539	NB 14-4 6-POLE
12801	NTSS-0150-46A SS
12801B	NTSS-0150-46A SS BLACK
12851	NTSS-0150-46B
12851B	NTSS-0150-46B COATED
12802	NTSS-0200-46A SS
12802B	NTSS-0200-46A SS BLACK
12852	NTSS-0200-46B
12852B	NTSS-0200-46B COATED
12821	NTSS-0200-79A SS
12821B	NTSS-0200-79A SS BLACK
12871	NTSS-0200-79B
12871B	NTSS-0200-79B COATED
12803	NTSS-0250-46A SS
12803B	NTSS-0250-46A SS BLACK
12853	NTSS-0250-46B
12853B	NTSS-0250-46B COATED
12822	NTSS-0250-79A SS
12822B	NTSS-0250-79A SS BLACK
12872	NTSS-0250-79B
12872B	NTSS-0250-79B COATED
12805	NTSS-0300-46A SS
12805B	NTSS-0300-46A SS BLACK
12855	NTSS-0300-46B
12855B	NTSS-0300-46B COATED
12824	NTSS-0300-79A SS
12824B	NTSS-0300-79A SS BLACK
12874	NTSS-0300-79B
12874B	NTSS-0300-79B COATED
12806	NTSS-0350-46A SS
12806B	NTSS-0350-46A SS BLACK
12856	NTSS-0350-46B
12856B	NTSS-0350-46B COATED
12825	NTSS-0350-79A SS
12825B	NTSS-0350-79A SS BLACK
12875	NTSS-0350-79B
12875B	NTSS-0350-79B COATED
12808	NTSS-0400-46A SS
12808B	NTSS-0400-46A SS BLACK
12858	NTSS-0400-46B

12858B	NTSS-0400-46B COATED
12827	NTSS-0400-79A SS
12827B	NTSS-0400-79A SS BLACK
12877	NTSS-0400-79B
12877B	NTSS-0400-79B COATED
12810	NTSS-0500-46A SS
12810B	NTSS-0500-46A SS BLACK
12860	NTSS-0500-46B
12860B	NTSS-0500-46B COATED
12829	NTSS-0500-79A SS
12829B	NTSS-0500-79A SS BLACK
12879	NTSS-0500-79B
12879B	NTSS-0500-79B COATED
12812	NTSS-0600-46A SS
12812B	NTSS-0600-46A SS BLACK
12862	NTSS-0600-46B
12862B	NTSS-0600-46B COATED
12831	NTSS-0600-79A SS
12831B	NTSS-0600-79A SS BLACK
12881	NTSS-0600-79B
12881B	NTSS-0600-79B COATED
12833	NTSS-0700-79A SS
12833B	NTSS-0700-79A SS BLACK
12883	NTSS-0700-79B
12883B	NTSS-0700-79B COATED
12814	NTSS-0800-46A SS
12814B	NTSS-0800-46A SS BLACK
12864	NTSS-0800-46B
12864B	NTSS-0800-46B COATED
12834	NTSS-0800-79A SS
12834B	NTSS-0800-79A SS BLACK
12884	NTSS-0800-79B
12884B	NTSS-0800-79B COATED
12836	NTSS-1000-79A SS
12836B	NTSS-1000-79A SS BLACK
12886	NTSS-1000-79B
12886B	NTSS-1000-79B COATED
S6507	REVRUNNER CLIP 100 PACK
S6547	REVRUNNER CLIP BULK
M4830GAN	SCG 1.093 BLACK 2-7.4MM

M4830GAQ	SCG 1.093 BLACK 2-8.0MM
M4830GBD	SCG 1.093 BLACK 3-4.6MM
M4830GAF	SCG 1.093 BLACK 3-5.2MM
M4830GAM	SCG 1.093 BLACK 3-7.0MM
M4830GBE	SCG 1.093 BLACK 4-4.6MM
M4830GAG	SCG 1.093 BLACK 4-5.2MM
M4836GAN	SCG 1.125 BLACK 2-7.4MM
M4836GAQ	SCG 1.125 BLACK 2-8.0MM
M4836GBD	SCG 1.125 BLACK 3-4.6MM
M4836GAF	SCG 1.125 BLACK 3-5.2MM
M4836GAM	SCG 1.125 BLACK 3-7.0MM
M4836GBE	SCG 1.125 BLACK 4-4.6MM
M4836GAG	SCG 1.125 BLACK 4-5.2MM
M4818GAB	SCG 875 BLACK 2-4.2MM
M4818GAE	SCG 875 BLACK 2-5.2MM
M8437GCC-SM	SMCG 1 NPT 3-8.3 + 6-3.3MM W/N
M8437GBT-SM	SMCG 1 NPT BLK 5-7.7MM W/2252
M8437GBK-SM	SMCG 1 NPT BLK 9-5.5MM W/2252
M3231GCF-SM	SMCG 1/2NPT 2-0.8+1-6MM W/2250
M3231GCP-SM	SMCG 1/2NPT 6.0+5-0.8MM W/2250
M3317GBZ-SM	SMCG 1-1/2 NPT 11-7.7MM W/9807
M3317GBQ-SM	SMCG 1-1/2NPT 21-5.5MM W/9807
M4522GBW-SM	SMCG 1-1/4 NPT BLK 9-7.7MM N/N
M3321GCM-SM	SMCG 2 NPT BLK 12-8.9MM W/9808
M3321GBX-SM	SMCG 2 NPT BLK 19-7.7MM W/9808
M3321GBY-SM	SMCG 2 NPT BLK 31-5.5MM W/9808
M3234GBS-SM	SMCG 3/4NPT BLK 3-7.7MM W/2251
M3234GBR-SM	SMCG 3/4NPT BLK 5-5.5MM W/2251
M4520GCQ-SM	SMCG LL1/2 NPT BLK 4-4.8MM N/N
M3200GAH-SM	SMCG LL1/2NPT BK 3-5.6MM W2250
M3200GCQ-SM	SMCG LL1/2NPT BK 4-4.8MM W/NUT
M3317GCK-SM	SMCG1-1/2NPT BLK 9-8.9MMW/9807
M4524GCJ-SM	SMCG1-1/4NPTBLK 7-8.9MM W/9806
M4524GBW-SM	SMCG1-1/4NPTBLK 9-7.7MM W/9806
M4524GBM-SM	SMCG1-1/4NPTBLK13-5.5MM W/9806
S6481	SSGS 1000-320
S6482	SSGS 1250-320
S6480	SSGS 750-320
S6410	SUNBUNDLER® 10-100 PACK
S6411	SUNBUNDLER® 10-BULK

S6412	SUNBUNDLER® 12-100 PACK
S6413	SUNBUNDLER® 12-BULK
S6414	SUNBUNDLER® 14-100 PACK
S6415	SUNBUNDLER® 14-BULK
S6421	SUNBUNDLER® 20- BULK
S6420	SUNBUNDLER® 20-100 PACK
S6408	SUNBUNDLER® 8-100 PACK
S6409	SUNBUNDLER® 8-BULK
S6511	SUNJUMPER 11
S6424	SUNBUNDLER 24-100 PACK
S6425	SUNBUNDLER 24-BULK
S6426	SUNBUNDLER 28-100 PACK
S6427	SUNBUNDLER 28-BULK
S6428	SUNBUNDLER 32-100 PACK
S6429	SUNBUNDLER 32-BULK
S6518	SUNJUMPER 18
S6506	SUNJUMPER 6
S6404	SUNRUNNER 2 CLIP 100/BAG
S6444	SUNRUNNER 2 CLIP BULK
S6463	SUNRUNNER 2 UVX 100 PACK
S6473	SUNRUNNER 2 UVX BULK
S6402	SUNRUNNER 2-R CLIP 100/BAG
S6442	SUNRUNNER 2-R CLIP BULK
S6462	SUNRUNNER 2-R UVX 100 PACK
S6472	SUNRUNNER 2-R UVX BULK
S6448	SUNRUNNER 2-S 100 PACK
S6488	SUNRUNNER 2-S BULK
S6401	SUNRUNNER 2-U CLIP 100/BAG
S6441	SUNRUNNER 2-U CLIP BULK
S6461	SUNRUNNER 2-U UVX 100 PACK
S6471	SUNRUNNER 2-U UVX BULK
S6400	SUNRUNNER 4 CLIP 100/BAG
S6440	SUNRUNNER 4 CLIP BULK
S6504	SUNRUNNER 4-2 100 PACK
S6544	SUNRUNNER 4-2 BULK
S6505	SUNRUNNER 4-2U 100 PACK
S6545	SUNRUNNER 4-2U BULK
S6406	SUNRUNNER 90 CLIP 100/BAG
S6446	SUNRUNNER 90 CLIP BULK
S6436	SUNRUNNER 90-2 100 PACK
S6476	SUNRUNNER 90-2 BULK

S6405	SUNRUNNER CLIP 100/BAG
S6445	SUNRUNNER CLIP BULK
S6434	SUNRUNNER CT 100 PACK
S6474	SUNRUNNER CT BULK
S6435	SUNRUNNER CT EZ 100 PACK

S6475	SUNRUNNER CT EZ BULK
S6447	SUNRUNNER EZ BULK
S6407	SUNRUNNER EZ CLIP 100/BAG
S6490	SUNRUNNER® 100 PACK
S6443	SUNRUNNER® 4 CLIP 100 PACK
S6483	SUNRUNNER® 4 CLIP BULK
S6439	SUNRUNNER® 90 - 4 CLIP 100 PACK
S6479	SUNRUNNER® 90 - 4 CLIP BULK
S6495	SUNRUNNER® BULK
S6460	SUNRUNNER® VIDRIO™ 100 PACK
S6500	SUNRUNNER® VIDRIO™ BULK
S6464	SUNSCREEN 4" PVC COATED 100' ROLL
S6466	SUNSCREEN 6" PVC COATED 100' ROLL
S6468	SUNSCREEN 8" PVC COATED 100' ROLL
S6438	SUNSCREENER CLIP BLACK
S6437	SUNSCREENER CLIP SS