

Gold Option	Gold Mouser Part Number	Cost-Optimized Alternative	Cost-Optimized Alternative Mouser Part Number
IPL1-102-01-H-D-K	200-IPL110201HDK	IPL1-102-01-L-D-K	200-IPL110201LDK
IPL1-102-01-S-D-K	200-IPL110201SDK	IPL1-102-01-L-D-K	200-IPL110201LDK
IPL1-102-01-S-D-RA-K	200-IPL110201SDRAK	IPL1-102-01-L-D-RA-K	200-IPL110201LDRAK
IPL1-102-02-S-D-K	200-IPL110202SDK	IPL1-102-02-L-D-K	200-IPL110202LDK
IPL1-102-02-S-D-K-TR	200-IPL110202SDKTR	IPL1-102-02-L-D-K-TR	200-IPL110202LDKTR
IPL1-103-01-H-D-K	200-IPL110301HDK	IPL1-103-01-L-D-K	200-IPL110301LDK
IPL1-103-01-S-D-K	200-IPL110301SDK	IPL1-103-01-L-D-K	200-IPL110301LDK
IPL1-103-01-S-D-RA-K	200-IPL110301SDRAK	IPL1-103-01-L-D-RA-K	200-IPL110301LDRAK
IPL1-103-01-S-S-K	200-IPL110301SSK	IPL1-103-01-L-S-K	200-IPL110301LSK
IPL1-104-01-S-D-K	200-IPL110401SDK	IPL1-104-01-L-D-K	200-IPL110401LDK
IPL1-104-01-S-D-RA-K	200-IPL110401SDRAK	IPL1-104-01-L-D-RA-K	200-IPL110401LDRAK
IPL1-104-01-S-S-K	200-IPL110401SSK	IPL1-104-01-L-S-K	200-IPL110401LSK
IPL1-104-02-S-D-K	200-IPL110402SDK	IPL1-104-02-L-D-K	200-IPL110402LDK
IPL1-105-01-S-D-K	200-IPL110501SDK	IPL1-105-01-L-D-K	200-IPL110501LDK
IPL1-105-01-S-D-P	200-IPL110501SDP	IPL1-105-01-L-D-P	200-IPL110501LDP
IPL1-105-01-S-D-RA-K	200-IPL110501SDRAK	IPL1-105-01-L-D-RA-K	200-IPL110501LDRAK
IPL1-105-01-S-S-K	200-IPL110501SSK	IPL1-105-01-L-S-K	200-IPL110501LSK
IPL1-105-01-S-S-RA-K	200-IPL110501SSRAK	IPL1-105-01-L-S-RA-K	200-IPL110501LSRAK
IPL1-105-02-S-D-K	200-IPL110502SDK	IPL1-105-02-L-D-K	200-IPL110502LDK
IPL1-106-01-H-D-K	200-IPL110601HDK	IPL1-106-01-L-D-K	200-IPL110601LDK
IPL1-106-01-S-D-RA-K	200-IPL110601SDRAK	IPL1-106-01-L-D-RA-K	200-IPL110601LDRAK
IPL1-107-01-S-S-K	200-IPL110701SSK	IPL1-107-01-L-S-K	200-IPL110701LSK
IPL1-109-01-S-D-RA-K	200-IPL110901SDRAK	IPL1-109-01-L-D-RA-K	200-IPL110901LDRAK
IPL1-110-01-H-D-K	200-IPL111001HDK	IPL1-110-01-L-D-K	200-IPL111001LDK
IPL1-110-01-S-D-K	200-IPL111001SDK	IPL1-110-01-L-D-K	200-IPL111001LDK
IPL1-110-01-S-D-P	200-IPL111001SDP	IPL1-110-01-L-D-P	200-IPL111001LDP
IPL1-110-01-S-D-RA-K	200-IPL111001SDRAK	IPL1-110-01-L-D-RA-K	200-IPL111001LDRAK

Gold Option	Gold Mouser Part Number	Cost-Optimized Alternative	Cost-Optimized Alternative Mouser Part Number
IPL1-110-01-S-S-K	200-IPL111001SSK	IPL1-110-01-L-S-K	200-IPL111001LSK
IPL1-110-02-S-D-K-TR	200-IPL111002SDKTR	IPL1-110-02-L-D-K-TR	200-IPL111002LDKTR
IPL1-111-01-S-D-K	200-IPL111101SDK	IPL1-111-01-L-D-K	200-IPL111101LDK
IPL1-112-02-S-D-K-TR	200-IPL1-11202SDKTR	IPL1-112-02-L-D-K-TR	200-IPL111202LDKTR
IPL1-114-01-H-D-K	200-IPL111401HDK	IPL1-114-01-L-D-K	200-IPL111401LDK
IPL1-115-01-S-D-K	200-IPL111501SDK	IPL1-115-01-L-D-K	200-IPL111501LDK
IPL1-115-01-S-D-RA-K	200-IPL111501SDRAK	IPL1-115-01-L-D-RA-K	200-IPL111501LDRAK
IPL1-115-01-S-D-RE1-K-WT	200-IPL11151SDRE1KWT	IPL1-115-01-L-D-RE1-K-WT	200-IPL11151LDRE1KWT
IPL1-115-02-S-D-K-TR	200-IPL111502SDKTR	IPL1-115-02-L-D-K-TR	200-IPL111502LDKTR
IPL1-120-01-S-D-K	200-IPL112001SDK	IPL1-120-01-L-D-K	200-IPL112001LDK
IPL1-120-01-S-D-RA-K	200-IPL112001SDRAK	IPL1-120-01-L-D-RA-K	200-IPL112001LDRAK