

Product Launch

USA

MOC

Versatile. Secure. That's MOC. HellermannTyton's comprehensive family of tube and pipe routing clips means unlimited possibilities for alternative energies, white goods and industrial automation applications.

PRODUCT INFORMATION

Our patented design results in superior retention, preventing inadvertent disengagement under vibration and during assembly processes such as vacuum fill. Yet, these products quickly and easily attach to routings to help installers maintain high productivity.

Of course, there's always room for a new configuration in the event your unique application warrants it. Need to add a third or fourth clip or a different mount? Let's work together to route your tubes and wiring in the most efficient and effective way possible.



Tube Separating and Routing

FEATURES & BENEFITS

- Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement
- Product combination possibilities offer versatility with clamps, ties and fastener options.
- Independent rotation allows for adjustable routing orientation.
- Fir tree options demonstrate easy insertion with high extraction resistance.
- Modular design allows custom builds to meet specific needs and requests with 360+ standard configurations.



MOC with Fir Tree

TECHNICAL DATA

Material :
PA66HIRHSUV

Operating Temperature:
-40°F to +230°F (-40°C to +110°C)

Flammability:
UL 94 HB

MARKETS

- Alternate Energies
- Industrial Automation
- Panel Shops
- HVAC
- White Goods

AVAILABILITY

- Parts are currently available in stock.
- Larger volume orders will be directed toward bulk quantity part numbers, which are also stocked items.
- Product Category Manager – Missy DeBord. Sample pack requests – Megan Gliebe or Jamison Soya

OPTIONAL INFO

- MOC Configurator for easily defining part configurations can be found at:

<https://www.hellermanntyton.us/modular-omega-clip-configurator/>

- Complete listing of MOC/LOC product line – LITPD341
- Current Sample Pack – SPLMOCLOC
- Packaged 100 per bag

Product Launch

MOC Configurations

HellermannTyton's comprehensive family of tube and pipe routing clips means unlimited possibilities for alternative energies, white goods and industrial automation applications.

Part Listing:

Part Number	Local Order Number	DESCRIPTION	Package Quantity
MOC -			
156-04239	156-04239	MOC Clip to MOC Clip, 12 mm, 12 mm, PA66HIRHSUV, Black, 100/bag	100 Pieces
156-04240	156-04240	MOC Clip to MOC Clip, 16 mm, 16 mm, PA66HIRHSUV, Black, 100/bag	100 Pieces
156-04241	156-04241	MOC Clip, 12 mm, Assembled to T50SMVC Swivel Tie, PA66HIRHSUV, Black, 100/bag	100 Pieces
156-04242	156-04242	MOC Clip, 16 mm, Assembled to T50SMVC Swivel Tie, PA66HIRHSUV, Black, 100/bag	100 Pieces
156-04243	156-04243	MOC Clip, 19 mm, Assembled to T50SMVC Swivel Tie, PA66HIRHSUV, Black, 100/bag	100 Pieces
156-04244	156-04244	MOC Clip, 26 mm, Assembled to T50SMVC Swivel Tie, PA66HIRHSUV, Black, 100/bag	100 Pieces
151-03821	151-03821	MOC Clip, 7 mm, with 6.5mm Fir Tree, PA66HIRHSUV, Black, 100/bag	100 Pieces
151-03822	151-03822	MOC Clip, 12 mm, with 6.5mm Fir Tree, PA66HIRHSUV, Black, 100/bag	100 Pieces
151-03823	151-03823	MOC Clip, 19 mm, with 6.5mm Fir Tree, PA66HIRHSUV, Black, 100/bag	100 Pieces
156-04239	156-04239	MOC Clip to MOC Clip, 12 mm, 12 mm, PA66HIRHSUV, Black, 100/bag	100 Pieces