




SOIC-24 to DIP-24 Narrow SMT Adapter

Compact Series Extra Narrow




REF.	DIMENSIONS					
	mm			inches		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A		3.65				
B		3.51				
C		0.64				
D		0.63				
E		1.27				
F					0.300	
G					0.100	
H		0.46				
X					0.450	
Y					1.200	

Top View (SMT Footprint)




(Representative drawing only - not to scale)

Bottom View (DIP Pins)



(Representative drawing only - not to scale)

Side View (DIP Pins)



(Representative drawing only - not to scale)