

# Water Heating System >

| Product Name    | Pitch             | Glow Wire | UL 94 V-0 | Secondary Lock | Plating              | Connection Style |        | PCB Termination |              | Colors/ Keys | IP Rated   |
|-----------------|-------------------|-----------|-----------|----------------|----------------------|------------------|--------|-----------------|--------------|--------------|------------|
|                 |                   |           |           |                |                      | W-to-B           | W-to-W | SMT             | Through Hole |              |            |
| Pico Blade      | 1.25mm            | --        | •         | --             | Tin/Gold             | •                | --     | •               | --           | --           | --         |
| Micro Lock Plus | 1.25/1.50/2.0mm   | --        | •         | --             | Tin / Gold Flash     | •                | •      | •               | --           | •            | --         |
| Clik Mate       | 1.25/1.5/2.0mm    | --        | •         | --             | Tin/Gold             | •                |        | •               | •            | --           | --         |
| Spot On         | 1.5, 2.0mm        | --        | •         | •              | Tin                  | •                | •      | •               |              | •            | --         |
| Micro One       | 2.0mm             | •         | •         | •              | Tin                  | •                | --     | •               | •            | --           | --         |
| Mini Lock       | 2.5mm             | •         | •         | •              | Tin                  | •                | --     | --              | --           | •            | --         |
| CP              | 2.5/3.3/4.5mm     | •         | •         | •              | Tin/Gold             | •                | •      | --              | --           | •            | --         |
| MUO             | 2.50mm            | --        | •         | •              |                      | •                | •      | --              | --           | •            | --         |
| Nano Fit        | 2.5mm             | •         | •         | •              | Tin/Gold             | •                | •      | •               | •            | •            | --         |
| Micro TPA       | 2.0mm             | •         | •         | •              | Tin/ Matte Tin/ Gold | •                | •      | •               | •            | •            | --         |
| Mini Fit        | 4.2mm             | •         | •         | •              | Tin/Gold             | •                | •      | •               | •            | •            | IP67 Rated |
| Micro Fit+      | 3.00mm            | •         | •         | •              | Tin/ Gold            | •                | •      | •               | •            | •            | --         |
| Mega Fit        | 5.7mm             | •         | •         | •              | Tin/Gold/Matte Tin   | •                | •      | --              | •            | •            | --         |
| CP              | 6.5mm             | •         | •         | •              | Tin/Gold             | •                | •      | --              | --           | •            | --         |
| MP Lock         | 187 in and 250 in | •         | •         | •              | Tin/Nickel Plating   | --               | --     | --              | --           | •            | --         |
| NTC             | N/A               | --        | •         | --             | Nickel               | --               | --     | --              | --           | --           | --         |
| Squba           | 1.8mm, 3.6mm      | •         | •         | --             | Tin                  | •                | •      | --              | --           | •            | IP68 Rated |

Available

•

Not Available

--