



Sherex Fastening Solutions, LLC.

400 Riverwalk Pkwy, Suite 600

Tonawanda, NY 14150

Toll Free: 866.474.3739

Tel: 716.875.0315

Fax: 716.875.0358

Email: info@sherex.com

SSG 800 Pistol Style Series

Designed for installing steel or aluminum **CAL, CAK, CAH, CAO, CFT/CAT*, CFW/CAW*, and CPB** Rivet Nut Inserts (thin wall only).

Features quick change nose piece for head set replacement without tools. *Can install these parts in stainless steel

Spin-Spin tools are also available in an Inline Version and a Right Angle Inline Version for difficult to access applications.

High temperature grease should be used to lubricate the bearing set.

Sherex recommends the use of an air regulator, air filter, and

[+ more](#)



1

Item #	Thread Size	Tool Speed	Air Pressure	Weight
<u>SSG-801-0440</u>	#4-40	3000 rpm	35-45 psi (2.4-3.1 bars)	3.0 lbs (1.4 kg)

Item #	Thread Size	Tool Speed	Air Pressure	Weight
<u>SSG-801-0632</u>	#6-32	3000 rpm	70-80 psi (4.8-5.5 bars)	3.0 lbs (1.4 kg)
<u>SSG-801-0832</u>	#8-32	3000 rpm	70-90 psi (4.8-6.2 bars)	3.0 lbs (1.4 kg)
<u>SSG-801-M3</u>	M3	3000 rpm	35-45 psi (2.4-3.1 bars)	3.0 lbs (1.4 kg)
<u>SSG-801-M4</u>	M4	3000 rpm	35-45 psi (2.4-3.1 bars)	3.0 lbs (1.4 kg)
<u>SSG-802-1024</u>	#10-24	1500 rpm	60-80 psi (4.1-5.5 bars)	3.0 lbs (1.4 kg)
<u>SSG-802-1032</u>	#10-32	1500 rpm	60-80 psi (4.1-5.5 bars)	3.0 lbs (1.4 kg)
<u>SSG-802-2520</u>	1/4-20	1500 rpm	70-90 psi (4.8-6.2 bars)	3.0 lbs (1.4 kg)
<u>SSG-802-2528</u>	1/4-28	1500 rpm	70-90 psi (4.8-6.2 bars)	3.0 lbs (1.4 kg)
<u>SSG-802-M5</u>	M5	1500 rpm	70-80 psi (4.8-5.5 bars)	3.0 lbs (1.4 kg)
<u>SSG-802-M6</u>	M6	1500 rpm	70-80 psi (4.8-5.5 bars)	3.0 lbs (1.4 kg)
<u>SSG-803-3118</u>	5/16-18	600 rpm	80-110 psi (5.5-7.6 bars)	3.0 lbs (1.4 kg)
<u>SSG-803-3124</u>	5/16-24	600 rpm	80-110 psi (5.5-7.6 bars)	3.0 lbs (1.4 kg)
<u>SSG-803-3716</u>	3/8-16	600 rpm	80-110 psi (5.5-7.6 bars)	3.0 lbs (1.4 kg)
<u>SSG-803-3724</u>	3/8-24	600 rpm	80-110 psi (5.5-7.6 bars)	3.0 lbs (1.4 kg)

Item #	Thread Size	Tool Speed	Air Pressure	Weight
<u>SSG-803-</u> <u>M8</u>	M8	600 rpm	80-110 psi (5.5-7.6 bars)	3.0 lbs (1.4 kg)
<u>SSG-803-</u> <u>M10</u>	M10	600 rpm	80-110 psi (5.5-7.6 bars)	3.0 lbs (1.4 kg)
<u>SSG-808-</u> <u>5013</u>	1/2-13	275 rpm	75-120 psi (5.2-8.3 bars)	4.0 lbs (1.8 kg)
<u>SSG-808-</u> <u>5020</u>	1/2-20	275 rpm	75-120 psi (5.2-8.3 bars)	4.0 lbs (1.8 kg)
<u>SSG-808-</u> <u>M12</u>	M12	275 rpm	75-120 psi (5.2-8.3 bars)	4.0 lbs (1.8 kg)