



Sherex Fastening Solutions, LLC.

400 Riverwalk Pkwy, Suite 600

Tonawanda, NY 14150

Toll Free: 866.474.3739

Tel: 716.875.0315

Fax: 716.875.0358

Email: info@sherex.com

SSG 900 Inline Style Series

Designed for installing steel or aluminum **CAL, CAK, CAH, CAO, CFT/CAT*, CFW/CAW*, and CPB** Rivet Nut Inserts (thin wall only).

Features quick change nose piece for head set replacement without tools. *Can install these parts in stainless steel.

Spin-Spin tools are also available in a Pistol Grip Version and a Right Angle Inline Version for difficult to access applications.

High temperature grease should be used to lubricate the bearing set.

Sherex recommends the use of an air regulator, air filter,

[+ more](#)



1

Item #	Thread Size	Tool Speed	Air Pressure	Weight
<u>SSG-901-</u> <u>0440</u>	#4-40	3000 rpm	35-45 psi (2.4-3.1 bars)	2.0 lbs (0.9 kg)

Item #	Thread Size	Tool Speed	Air Pressure	Weight
<u>SSG-901-0632</u>	#6-32	3000 rpm	70-80 psi (4.8-5.5 bars)	2.0 lbs (0.9 kg)
<u>SSG-901-0832</u>	#8-32	3000 rpm	70-90 psi (4.8-6.2 bars)	2.0 lbs (0.9 kg)
<u>SSG-901-M3</u>	M3	3000 rpm	35-45 psi (2.4-3.1 bars)	2.0 lbs (0.9 kg)
<u>SSG-901-M4</u>	M4	3000 rpm	35-45 psi (2.4-3.1 bars)	2.0 lbs (0.9 kg)
<u>SSG-902-1024</u>	#10-24	1500 rpm	60-80 psi (4.1-5.5 bars)	2.0 lbs (0.9 kg)
<u>SSG-902-1032</u>	#10-32	1500 rpm	60-80 psi (4.1-5.5 bars)	2.0 lbs (0.9 kg)
<u>SSG-902-2520</u>	1/4-20	1500 rpm	70-90 psi (4.8-6.2 bars)	2.0 lbs (0.9 kg)
<u>SSG-902-2528</u>	1/4-28	1500 rpm	70-90 psi (4.8-6.2 bars)	2.0 lbs (0.9 kg)
<u>SSG-902-M5</u>	M5	1500 rpm	70-80 psi (4.8-5.5 bars)	2.0 lbs (0.9 kg)
<u>SSG-902-M6</u>	M6	1500 rpm	70-80 psi (4.8-5.5 bars)	2.0 lbs (0.9 kg)
<u>SSG-903-3118</u>	5/16-18	600 rpm	80-110 psi (5.5-7.6 bars)	2.0 lbs (0.9 kg)
<u>SSG-903-3124</u>	5/16-24	600 rpm	80-110 psi (5.5-7.6 bars)	2.0 lbs (0.9 kg)
<u>SSG-903-3716</u>	3/8-16	600 rpm	80-110 psi (5.5-7.6 bars)	2.0 lbs (0.9 kg)
<u>SSG-903-3724</u>	3/8-24	600 rpm	80-110 psi (5.5-7.6 bars)	2.0 lbs (0.9 kg)

Item #	Thread Size	Tool Speed	Air Pressure	Weight
<u>SSG-903-</u> <u>M8</u>	M8	600 rpm	80-110 psi (4.8-6.2 bars)	2.0 lbs (0.9 kg)
<u>SSG-903-</u> <u>M10</u>	M10	600 rpm	80-110 psi (4.8-6.2 bars)	2.0 lbs (0.9 kg)