



January 2025



## DUSH960-1248 Series

### Quick Facts:

- \* DIN Rail mount
- \* Uninterruptible DC Power Supplies
- \* 960W, 20A rated, 10 to 60Vdc input and output

[DATA SHEET](#)

### What are they?

Power supplies providing a back-up DC voltage if the input power is lost

- Input Voltage 10 to 60Vdc
- Output Voltages 10 to 60Vdc (20A). Optional 5A auxiliary voltage.
- Output Power 960W  
Up to 98% efficient, multiple battery types up to 1000Ah. LCD, RS485, USB and Modbus/RTU protocol interfaces for programming. DIN-rail mount. Battery temperature monitoring sensor. Multiple signal and alert functions.
- Features

### Where are they Used?

- Industrial automation
- Building control
- Test and measurement
- Communication systems



#### Why?

Addressing the need for DIN rail mount un-interruptible power sources



#### When?

**Distribution stock February 2025**



#### Samples?

Upon request

\*This document is an advanced notification of an upcoming product

*Knowledge is Power. Power is TDK-Lambda.*

[VISIT OUR WEBSITE](#)

[VISIT OUR BLOG](#)

Stay connected: