AUDIO TECHNOLOGIES®

12/2 CL3 PLENUM-RATED SPEAKER WIRE

SPECIFICATIONS

UL13 CL3P
(FLAMMABILITY RATING)

2
(NO. OF CONDUCTORS)

12 AWG
(CONDUCTOR SIZE)

STRANDED ANNEALED COPPER
(CONDUCTOR DETAILS)

WHITE
(JACKET COLOR)

RED, BLACK
(INSULATION COLORS)

LSFR PVC (Low Smoke, Flame Retardant)
(INSULATION MATERIAL)

CONDUCTORS
12 AWG stranded annealed copper for maximum flexibility



INSULATION
Red & black low smoke, flame retardant PVC for for safe, compliant installations

RIP CORD
Quick, damage-free jacket removal to simplify cable termination

JACKET
White PVC with dual-direction footage markings every 2 ft for fast, accurate cable measurement



Available in 500 ft Spools

★ MARKETS & APPLICATIONS

- Suitable for use in Class 3 power-limited circuits up to 300V
- Professional Audio Installations
- Commercial AV
- Multi-Room Residential Systems
- Paging
- Background Music Applications

★ FEATURES & BENEFITS

- Easy Polarity Identification: Red and Black Insulation
- Code Compliant: Plenum Rated (UL13 CL3P)
- Quick Cable Length Tracking: Footage Markings Every 2 FT
- Routing Ease: Durable Yet Flexible Jacket
- Integrated Ripcord: Enables Fast, Clean Stripping to Protect Internal Conductors