



VULCON™

Future of Circular Connector Technology

IP67/IP68 Performance / Compact Form Factors

VULCON™ Circular connectors offer a robust waterproof cable to panel interface for demanding end use applications. Available in 12mm, 8mm and 5mm diameters, these connectors offer a wide range of solutions for the most demanding design environments. Both the 12mm and 8mm product offerings conform to industry standard Bus specifications and are intermatable with a wide variety of competitive products.

FEATURES & BENEFITS

- Available in 3 sizes | 12mm, 8mm, & 5mm diameters
- Available in pin counts ranging from 2 to 12 positions
- IP67/IP68 Performance in both mated / unmated conditions
- Solder Cup, Vertical & Right Angle board mount options
- Cable mount available loose piece or as pre-made cables
- Up to 5 AMP contact rating / -40°C to +85°C
- Full metal shells for EMI/RFI shielding
- A, D X & L Codes now available



NORCOMP

M5 Series

Male Sizes

Female Sizes

Cable Mount

2,3,4

2,3,4

Panel Mount Solder Cup

2,3,4

2,3,4

Vertical Board Mount

2,3,4

2,3,4

Right Angle Board Mount

2,3,4

2,3,4

M8 Series

Male Sizes

Female Sizes

Cable Mount

3,4,5,6

3,4,5,6

Panel Mount Solder Cup

3,4,5,6

3,4,5,6

M12 Series - A Code

Male Sizes

Female Sizes

Cable Mount

3,4,5,8,12

3,4,5,8,12

Panel Mount Solder Cup

3,4,5,8,12

3,4,5,8,12

Vertical Board Mount

3,4,5,8,12

3,4,5,8,12

Right Angle Board Mount

3,4,5,8

3,4,5,8

M12 Series - D Code

Male Sizes

Female Sizes

Cable Mount

4

4

Panel Mount Solder Cup

4

4

Vertical Board Mount

4

4

M12 Series - X Code

Male Sizes

Female Sizes

Cable Mount

8

-

Panel Mount Solder Cup

-

8

Vertical Board Mount

-

8

M12 Series - L Code

Male Sizes

Female Sizes

Cable Mount

5

5

Panel Mount Solder Cup

5

5