

EMI FILTER SOLUTIONS

A GUIDE TO PROFESSIONAL-GRADE AND COMMERCIAL APPLIANCES



WASHER & DRYERS | DISWASHER

- ✓ Medium to high insertion loss levels to help comply with applicable limits
- ✓ Water ingress resistant
- ✓ Metalized film technology for high reliability
- ✓ SINGLE PHASE 3-16 A (Residential Applications)
- ✓ 3 PHASE 10-40 A (Commercial Applications)

EMI FILTER SOLUTIONS

- ↳ LCR 095 SERIES
- ↳ RP305 SERIES
- ↳ RP310 SERIES
- ↳ RP405 SERIES
- ↳ RP410 SERIES
- ↳ RP410 HP SERIES
- ↳ CUSTOM SOLUTION



BLENDERS | MIXERS

- ✓ Varying insertion loss levels can help comply with applicable limits
- ✓ Compact & ultra compact models
- ✓ Quick disconnect, wires, and special connectors
- ✓ SINGLE PHASE 1-20 A

EMI FILTER SOLUTIONS

- ↳ RP100 SERIES
- ↳ RP105 SERIES
- ↳ RP110 SERIES
- ↳ RP115 SERIES
- ↳ RP2180 SERIES
- ↳ CUSTOM SOLUTION



FLOOR CLEANING

- ✓ Medium insertion loss levels to help comply with applicable limits
- ✓ Water ingress resistant in some cases
- ✓ SINGLE PHASE 3-16 A

EMI FILTER SOLUTIONS

- ↳ RP100 SERIES
- ↳ RP105 SERIES
- ↳ RP115 SERIES
- ↳ RP2180 SERIES
- ↳ CUSTOM SOLUTION

THREADMILLS | STAIR CLIMBERS | ELLIPTICALS

- ✓ Medium to high insertion loss levels to help comply with applicable limits
- ✓ SINGLE PHASE 3-20 A

EMI FILTER SOLUTIONS

- ↳ RP100 SERIES
- ↳ RP105 SERIES
- ↳ RP110 SERIES
- ↳ RP115 SERIES
- ↳ RP120 SERIES
- ↳ RP130 SERIES
- ↳ RP210 SERIES
- ↳ RP220 SERIES
- ↳ RP225 SERIES
- ↳ RP230 SERIES
- ↳ DSC1000
- ↳ DSC2000
- ↳ CUSTOM SOLUTION



MICROWAVE OVEN | INDUCTION COOKTOPS

- ✓ Medium to high performance designs to bring high noise application within applicable limits
- ✓ SINGLE PHASE 3-20 A

EMI FILTER SOLUTIONS

- ↳ RP 110 SERIES
- ↳ RP 120 SERIES
- ↳ RP 130 SERIES
- ↳ RP 210 SERIES
- ↳ RP220 SERIES
- ↳ RP225 SERIES
- ↳ RP230 SERIES
- ↳ CUSTOM SOLUTION



REFRIGERATORS | CHILLERS

- ✓ Medium to high insertion loss levels to help comply with applicable limits
- ✓ Water ingress resistant
- ✓ Metalized film technology for high reliability
- ✓ SINGLE PHASE 3-20 A (Residential Applications)
- ✓ 3 PHASE 10-40 A (Commercial Applications)

EMI FILTER SOLUTIONS

- ↳ RP100 SERIES
- ↳ RP105 SERIES
- ↳ RP110 SERIES
- ↳ RP115 SERIES
- ↳ RP120 SERIES
- ↳ RP130 SERIES
- ↳ RP210 SERIES
- ↳ RP220 SERIES
- ↳ RP225 SERIES
- ↳ RP230 SERIES
- ↳ RP305 SERIES
- ↳ RP310 SERIES
- ↳ RP405 SERIES
- ↳ RP410HP SERIES
- ↳ 095 SERIES
- ↳ CUSTOM SOLUTION



COFFEE MACHINES | VENT HOODS

- ✓ Low to medium insertion loss levels to help comply with applicable limits
- ✓ IEC INLETS 1-20 A

EMI FILTER SOLUTIONS

- ↳ RP180 SERIES
- ↳ RP185 SERIES
- ↳ RP187 SERIES
- ↳ RP188 SERIES
- ↳ 080 SERIES
- ↳ 081 SERIES
- ↳ 082 SERIES
- ↳ 083 SERIES
- ↳ 084 SERIES
- ↳ 085 SERIES
- ↳ CUSTOM SOLUTION

