

CAPA13R NEW

3.5" Embedded SBC with AMD® RYZEN™ Embedded V1807B/V1605B APU, DisplayPort, 2 HDMI, LVDS and 4 GbE LAN

Features

- AMD® RYZEN™ Embedded V1807B and V1605B APU
- 1 DDR4 SO-DIMM for up to 16GB of memory
- 4 GbE LAN
- Supports quad-view
- M.2 Key E
- M.2 Key B



Core System



CPU	AMD® RYZEN™ Embedded V1807B/V1605B APU onboard
System Memory	1 x 260-pin DDR4-2400 (V1605B), DDR4-3200 (V1807) SO-DIMM, up to 16GB
Chipset	SoC integrated
BIOS	AMI
SSD	1 x M.2 Key B (SATA, USB 2.0, PCIe x2 for optional) in 22x42 or 30x42
Watchdog Timer	255 levels, 1 to 255 sec.
Expansion Interface	1 x M.2 Key E (PCIex1, USB2.0) in 22x30
Battery Lithium	Lithium 3V/220 mAh
Power Input	2 x 2 pin connector +12V DC-in only AT Auto Power On function supported
Power Requirement	AMD (R) V1605B @2.0 GHz 16GB DDR4, max. RMS. +12V@2.5A AMD (R) V1807B @3.8 GHz 16GB DDR4, max. RMS. +12V@4.2A
Dimensions	146 x 104 mm
Board Thickness	1.6 mm
Operating Temperature	-20°C to +60°C (-4°F to 140°F)
Humidity	10% - 95% relative humidity, non-condensing

I/O


SATA	1 x SATA-600
Hardware Monitoring	Detect CPU/system temperature, voltage and fan speed
Ethernet	2 x10/100/1000 Mbps Ethernet with Realtek RTL8111G; support Wake-on-LAN, PXE Boot ROM 2 x10/100/1000 Mbps Ethernet with Realtek RTL8111G; support Wake-on-LAN, PXE Boot ROM (optional)
Audio	HD audio link
USB	2 x USB 2.0 2 x USB 3.1 Gen2
Serial	1 x RS-232/422/485 1 x RS-232
TPM	ST ST33HTPH2E32AHB4 with TPM 2.0 compliant
SMBus	N/A
Digital I/O	8-channel in/out programmed

Display

Chipset	AMD® Radeon™ RX Vega Graphics
Memory Size	Share System memory
Display Interface	1 x DisplayPort 2 x HDMI 1 x LVDS; 18/24-bit single/dual channel



▲ Top view



▲ Rear view



▲ Assembly View

Ordering Information

Standard	
CAPA13RPHGG-V1605B (P/N: E38E13R104)	3.5" Embedded SBC with AMD® RYZEN™ V1605B (2.0 - 3.6 GHz, 2MB Cache, 15W) DisplayPort, 2 HDMI, LVDS and 2 GbE LAN, without fan
CAPA13RPHGG-V1605B w/fan (P/N: E38E13R108)	3.5" Embedded SBC with AMD® RYZEN™ V1605B (2.0 - 3.6 GHz, 2MB Cache, 15W) DisplayPort, 2 HDMI, LVDS, 2 GbE LAN and fan
CAPA13RPHGG-V1807B (P/N: E38E13R103)	3.5" Embedded SBC with AMD® RYZEN™ V1807B (3.35 - 3.8 GHz, 2MB Cache, 45W) DisplayPort, 2 HDMI, LVDS and 2 GbE LAN, without fan
CAPA13RPHGG-V1807B w/fan (P/N: E38E13R107)	3.5" Embedded SBC with AMD® RYZEN™ V1807B (3.35 - 3.8 GHz, 2MB Cache, 45W) DisplayPort, 2 HDMI, LVDS, 2 GbE LAN and fan

Optional	
CAPA13RPH4G-V1605B (P/N: E38E13R101)	3.5" Embedded SBC with AMD® RYZEN™ Embedded V1605B (2.0-3.6 GHz, 2MB Cache, 15W), DisplayPort, 2 HDMI, LVDS, and 4 GbE LAN, without fan
CAPA13RPH4G-V1605B w/fan (P/N: E38E13R106)	3.5" Embedded SBC with AMD® RYZEN™ Embedded V1605B (2.0-3.6 GHz, 2MB Cache, 15W), DisplayPort, 2 HDMI, LVDS, 4 GbE LAN, and fan
CAPA13RPH4G-V1807B (P/N: E38E13R100)	3.5" Embedded SBC with AMD® RYZEN™ Embedded V1807B (3.35-3.8 GHz, 2MB Cache, 45W), DisplayPort, 2 HDMI, LVDS, and 4 GbE LAN, without fan
CAPA13RPH4G-V1807B w/fan (P/N: E38E13R105)	3.5" Embedded SBC with AMD® RYZEN™ Embedded V1807B (3.35-3.8 GHz, 2MB Cache, 45W), DisplayPort, 2 HDMI, LVDS, 4 GbE LAN, and fan
AX93A22 (P/N: E393A22100)	HD codec audio board for Mic-in/Line-in/Line-out
594H3186800E	Buzzer cable 9 x 55 mm 2-pin, L=400 mm
59380880250E	COM port cable DB9-9 x 1P, P=1.25, L=250 mm
594E8422800E	2 x USB 2.0 cable with bracket, 180 mm
7128E13E3000E	Heatspreader