



Pushing Performance  
Since 1945

# Double-Indent Pneumatic Crimping Tool



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 99 000 1010                                                                |
| Specification      | Double-Indent Pneumatic Crimping Tool                                         |
| HARTING eCatalogue | <a href="https://harting.com/09990001010">https://harting.com/09990001010</a> |

## Identification

|                         |                                                                                                                                                                                                                          |
|-------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Category                | Tools                                                                                                                                                                                                                    |
| Type of tool            | Pneumatic crimping tool                                                                                                                                                                                                  |
| Description of the tool | Han D <sup>®</sup> : 0.14 ... 2.5 mm <sup>2</sup><br>Han E <sup>®</sup> : 0.14 ... 4 mm <sup>2</sup><br>Han <sup>®</sup> C: 1.5 ... 10 mm <sup>2</sup><br>D-Sub<br>Han <sup>®</sup> ORV3 power: 4 ... 10 mm <sup>2</sup> |
| Type of drive           | Pneumatic                                                                                                                                                                                                                |

## Version

|                       |                                                                                                                                                   |
|-----------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|
| Die set               | 4-mandrel two-indent crimp                                                                                                                        |
| Direction of movement | 4 indent                                                                                                                                          |
| Field of application  | Recommended for production lines<br>up to 50,000 crimping operations per year                                                                     |
| Pack contents         | Foot switch<br>Locator Han D <sup>®</sup><br>Locator Han E <sup>®</sup><br>Locator Han <sup>®</sup> C<br>Pneumatic tube<br>Operating instructions |

## Technical characteristics

|                              |       |
|------------------------------|-------|
| Cycles cleaning / inspection | 500   |
| Cycles crimp check           | 5,000 |



**Pushing Performance**  
Since 1945

## Technical characteristics

|                              |        |
|------------------------------|--------|
| Cycles service / maintenance | 50.000 |
|------------------------------|--------|

## Commercial data

|                                |                          |
|--------------------------------|--------------------------|
| Packaging size                 | 1                        |
| Net weight                     | 0.1 kg                   |
| Country of origin              | Germany                  |
| European customs tariff number | 84671900                 |
| GTIN                           | 5713140301153            |
| eCl@ss                         | 21043811 Crimping pliers |
| ETIM                           | EC000168                 |