

TECHNICAL DATA SHEET

Part No. 151-04370
Article No. 151-04370
Type BCFLGA



The Wedge Clip, paired with any HellermannTyton heavy duty cable tie, routes cables along a frame or rail in vertical or horizontal applications. A robust design and durable materials make it ideal for extreme-duty applications. The integrated wedge mechanism slides along a stepped grade until snug against the mounting surface. Inside the clip is a 3M™ VHB™ (Very High Bond) adhesive pad, which actually builds strength over time. This holds the clip to the work surface instantly, enabling installers to place it into position without worrying about it falling off prior to fastening. The combination of adhesive and the clip's vice-like compression result in incredible pull-off resistance without the need to drill holes.

Material	Polyamide 6.6, glass fiber reinforced (PA66GF30), Polyamide 6.6, glass-fibre reinforced (PA66GF35)
Operating Temperature	-40°F to +284°F (-40°C to +140°C)
Flammability	UL 94 HB
Halogen Free	No
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK), Gray (GY)
Pkg. Qty.	200
Carton Qty.	600 Pieces
Customs Number	3926909988

Fixation Method	Edge Clip
Height (imperial)	2.26 "
Height (metric)	57.3 mm
Length (imperial)	1.21 "
Length (metric)	30.8 mm
Max. Cable Tie Width (imperial)	0.60 "
Max. Cable Tie Width (metric)	15.01 mm
Panel Thickness (imperial)	0.83 - 0.98 "
Panel Thickness (metric)	21.0 - 25.0 mm
Width (imperial)	1.44 "
Width (metric)	36.5 mm

