



Product Selector
Complete capability in switching solutions

TW Switches

PRODUCT SELECTOR

	Series	Country of Production	Type	Thread M	O/D mm (in)	Contact	Material	Illumination	Momentary	Maintained / Latched	Configuration	Contact Arrangement	Operating Force (N)	Protection	Current (A)		Voltage (V)	Operating Life	
																		Electrical	Mechanical
	030	MX	Rotary	n/a	7.0	n/a	Metal	No	No	Yes	n/a	n/a		n/a	500mA	@	125V AC		10K
	034	MX	Pushbutton	n/a	9.14	SP	Metal	No	Yes	No	SPST-NO			n/a	100mA	@	125V AC		1 M
	11	MX	Microswitch	n/a	n/a	SP	Black Plastic	No	Yes	No	SPST-DB SPDT-DB SPDT-SB	Form Z	2.2	n/a	10A	@	250V AC		
	14	MX	Microswitch	n/a	n/a	SP	Black Plastic	No	Yes	No	SPDT-DB	Form Z	3.3	n/a	20A	@	480V AC		
	16	MX	Microswitch	n/a	n/a	SP / DP	Black Plastic	No	Yes	No	SPDT-DB	Form Z	2.2	IP40	10A	@	250V AC	100K	10 M
	18	US / BA	Microswitch	n/a	n/a	SP	Green Plastic	No	Yes	No	SPDT-DB	Form Z	2.2	IP40	8A	@	28V DC	10K	10 M
	19N	BA	Microswitch	n/a	n/a	SP	Green Plastic	No	Yes	No	SPDT-DB	Form C	<2.0	IP67	5A	@	250V AC	100K	10 M
	22	MX	Microswitch	n/a	n/a	SP	Black Plastic	No	Yes	No	DPDT-DB-NO	Form XX Form YY	4.7	n/a	8A	@	28V DC		
											DPDT-DB	Form ZZ							
	26	US	Microswitch	n/a	n/a	SP / DP	Black Plastic	No	Yes	No	DPDT-DB	Form ZZ	4.5	IP40	8A	@	250V AC	100K	10 M
	SA12	CN	Pushbutton	M12	17.4	SP	Black Plastic	Yes	Yes	No	SPDT-DB	Form Z	5.15N	IP67	5A	@	28V DC 125/250V AC	25K	25K
	48M	TW	Vandal Resistant	M19	21.6 (0.85)	SP	Stainless Steel	Yes	Yes	Yes	SPST-NO-DB	n/a	3N	IP67	10mA	@	12V DC Resistive		500K Momentary 100K Maintained

	Series	Country of Production	Type	Thread M	O/D mm (in)	Contact	Material	Illumination	Momentary	Maintained / Latched	Configuration	Contact Arrangement	Operating Force (N)	Protection	Current (A)		Voltage (V)	Operating Life	
																		Electrical	Mechanical
	59	BA/TW	Pushbutton	M12	17.5 (0.69)	SP	Black Plastic	No	Yes	No	SPST-NO	n/a	3N	IP67	100mA	@	50V DC	500K	1 M
	49-59T	US	Pushbutton	M16	20.0	SP / DP	Black Plastic	No	Yes	No	SPST-DB	Form Z	3.8N - 5.5N	IP67	10A	@	28V DC	50K	1 M
										DPDT-DB	Form ZZ								
	49-59W	BA	Pushbutton	M16	20.0	SP	Black Plastic	No	Yes	No	SPST-NO-DB	n/a	3N	IP67	100mA	@	50V DC	500K	1 M
	57	BA	Vandal Resistant	M16	18.5 (0.73)	SP	Chrome Plated	Yes	Yes	No	n/a	n/a	3N	IP67	100mA	@	50V DC	500K	1 M
	57M	TW	Vandal Resistant	M16	18.5 (0.73)	SP	Zinc Alloy	Yes	Yes	Yes	SPST-NO-DB	Form X	3N	IP67	10mA	@	12V DC		500K Momentary 25K Maintained
	65	US	Microswitch	n/a	n/a	SP	Metal	No	Yes	No	SPDT-DB	Form Z			10A	@	250V AC		
	76-6	BA	Microswitch	n/a	n/a	SP	Black Plastic	No	Yes	No	SPDT-DB	Form X Form Y Form Z			5A	@	250V AC		
	76-59	BA	Vandal Resistant	M19	21.6 (0.85)	SP	Stainless Steel	Yes			SPST-NO-DB	Form X	3N	IP67	125mA	@	125V AC	500K	1 M
		US	Vandal Resistant	M19	20.5 (0.85)	SP		No							100mA		50V DC		
	76-91	BA	Pushbutton	22.5	30.0	SP / DP	Black Plastic	Yes	Yes	No	SPDT-DB	Form Z	12N	IP67	10mA 10A	@	5V DC 250V AC	100K	1 M
	76-94	BA	Vandal Resistant	22.5	30.0 - 46.5	SP / DP	Painted Zinc	No	Yes	Yes	SPDT-DB DPDT-DB	Form Z Form ZZ	7N	IP67	10A max	@	250V AC	100K	2 M Pushbutton 100K Maintained Pushbutton 50K Rotary
	76-95	BA	Vandal Resistant	M19	21.6 (0.85)	SP / DP	Stainless Steel	No	Yes	No	SPDT-DB	Form X Form Y	2.6N	IP67	10A	@	28V DC	50K	1 M
											DPDT-DB	Form Z			5A		250V AC		
	76-97	BA	Pushbutton	22.5	30	SP	Black Plastic	No	Yes	Yes	SPDT-DB	Form Z	12N	IP67	10A	@	250V AC	100K	2 M
						DP					DPDT-DB	Form ZZ							

LRN10004-2. 07-2023



195 E Algonquin Road,
Des Plaines IL 60016. USA

www.itwswitches.com



Edgington Way, Sidcup,
Kent, UK, DA14 5EF