

ELECTRONICS CLEANERS COMPARISON CHART

	AEROSOL					LIQUID			
Product name	ISOPROPYL ALCOHOL	SAFETYWASH II™	SUPERWASH™	HFE SOLVENT	SUPER HFE SOLVENT	ISOPROPYL ALCOHOL LIQUID	ISOPROPYL ALCOHOL 70/30	SAFETYWASH™ LIQUID	ACETONE
Cat. Number	824-450G	4050A	406B	411	4120	824	8241	4050	434
PLASTIC SAFE	YES	YES	YES	YES	TEST	YES	YES	YES	NO
FLAMMABLE	YES	YES	YES	NO	NO	YES	YES	YES	YES
STRENGTH	REGULAR	ENHANCED	EXTRA	REGULAR	EXTRA	REGULAR	REGULAR	REGULAR	EXTRA
EVAPORATION	SLOW	SLOW	SUPER FAST	ULTRA FAST	ULTRA FAST	SLOW	SLOW	SLOW	ULTRA FAST
NSF COMPLIANT	NO	YES	YES	YES	YES	YES	NO	NO	NO
RESIDUE	NO	NO	NO	NO	NO	NO	NO	NO	NO
VOC FREE	NO	NO	NO	YES	YES	NO	NO	NO	YES
FLASH POINT	-88 °C / -126 °F	-29 °C / -20 °F	-29 °C / -20 °F	NONE	NONE	12 °C / 54 °F	18 °C / 64 °F	78 °C / 174 °F	-17 °C / 1.4 °F
BOILING POINT	81.8 °C / 179 °F	50 °C / 121 °F	50 °C / 121 °F	60 °C / 140 °F	40 °C / 104 °F	82 °C / 179 °F	81 °C / 177 °F	78 °C / 174 °F	-17 °C / 1.4 °F