



ORION FANS

We'll make You a fan



ATEX EC Fans

Spark Proof Protection for Hazardous Locations



Orion Fans IP68-ATEX rated EC fans grant protection in explosive gas atmospheres while also providing significant cost and energy savings. When employed in Zone 2 applications, ATEX fans eradicate the potential of a motor spark and explosion making them the leading choice for use around flammable gases. With the added IP68-rating, these fans effectively protect against dust and can also be submerged in water of depths up to three meters.

Features and Benefits

- Designed for use in Zone 2 Group IIC Hazardous Locations
- Meets Directive 2014/34/EU
- PBT, UL94V-0 plastic or Aluminum die-cast frames
- Dual ball bearing system design
- Available in 60mm-254mm frame sizes
- Applications: Zone 2 Equipment, Appliances, Commercial & Process Control, Refrigeration, HVAC, Electronic Enclosures, and Cabinets

Orion Fans

10557 Metric Drive
Dallas, TX 75243

Ph: 214.340.0265
Fx: 214.340.5870

www.orionfans.com