

# TRIM

## Commercial & Military SWITCH MODELS



| SERIES              | FEATURE                                                       | ACTUATION                                                  | MAX RATING<br>(Resistive)                          | SEAL RATING                                                                               | MOUNTING                                | CIRCUITRY                          |
|---------------------|---------------------------------------------------------------|------------------------------------------------------------|----------------------------------------------------|-------------------------------------------------------------------------------------------|-----------------------------------------|------------------------------------|
| T1<br>(mini)        | 2-Way<br>Quiet Operation                                      | Momentary                                                  | 10mA @ 5VDC<br>(logic level)                       | IP6K4, IP6K8S,<br>Watertight per<br>MIL-PRF-8805 Design 3                                 | 11/16" dia.<br>Threaded<br>or Press Fit | SPST (x2)                          |
| T1-T<br>(mini)      | 2-Way<br>Tactile Feedback                                     | Momentary/<br>Maintained                                   | 2A @ 28VDC<br>or 10mA @ 5VDC<br>(logic level)      | Water Resistant per<br>MIL-PRF-810F, Method<br>506.4 Procedure 3 (Drip)                   | 11/16" dia.<br>Threaded                 | SPST (x2)                          |
| T2<br>(mini)        | 2-Way<br>Quiet Operation<br>Center Pushbutton                 | Momentary                                                  | 10mA @ 5VDC<br>(logic level)                       | IP6K4, IP6K8S,<br>Watertight per<br>MIL-PRF-8805 Design 3                                 | 11/16" dia.<br>Threaded<br>or Press Fit | SPST (x3)                          |
| T4<br>(mini)        | 4-Way<br>Quiet Feedback                                       | Momentary                                                  | 10mA @ 30mV<br>(low level)                         | IP6K4, IP6K8S,<br>Watertight per<br>MIL-PRF-8805 Design 3                                 | 11/16" dia.<br>Threaded<br>or Press Fit | SPST (x4)                          |
| T4-T<br>(mini)      | 4-Way<br>Tactile Feedback                                     | Momentary<br>with<br>Tactile Feel                          | 2A @ 28VDC<br>or 10mA @ 5VDC<br>(logic level)      | IP6K4, IP6K8S,<br>Water Resistant per<br>MIL-PRF-810F, Method<br>506.4 Procedure 3 (Drip) | 3/4" dia. Threaded<br>or Press Fit      | SPST (x4)                          |
| T5<br>(mini)        | 4-Way<br>Quiet Operation<br>Center Pushbutton                 | Momentary,<br>Lenient Option                               | 10mA @ 5VDC<br>(logic level)                       | IP6K4, IP6K8S,<br>Watertight per<br>MIL-PRF-8805 Design 3                                 | 11/16" dia.<br>Threaded<br>or Press Fit | SPST (x5)                          |
| T8<br>(mini)        | 8-Way<br>Quiet Operation                                      | Momentary                                                  | 10mA @ 5VDC<br>(logic level)                       | IP6K4, IP6K8S,<br>Watertight per<br>MIL-PRF-8805 Design 3                                 | 11/16" dia.<br>Threaded<br>or Press Fit | SPST (x8)                          |
| T8-T<br>(mini)      | 8-Way<br>Tactile Feedback                                     | Momentary<br>with<br>Tactile Feel                          | 2A @ 28VDC<br>or 10mA @ 5VDC<br>(logic level)      | IP6K4, IP6K8S,<br>Water Resistant per<br>MIL-PRF-810F, Method<br>506.4 Procedure 3 (Drip) | 3/4" dia. Threaded<br>or Press Fit      | SPST (x8)                          |
| TK<br>(mini)        | 4-Way or<br>4-Way w/ Center<br>Pushbutton<br>Tactile Feedback | Momentary<br>with<br>Tactile Feel                          | 50mA @ 12VDC<br>(logic level)                      | IP6K4, IP6K8S,<br>or Unsealed                                                             | 5/8" dia. Threaded                      | SPST (x4)<br>or<br>SPST (x5)       |
| SPT<br>(split trim) | Two 2-Way<br>Trim Switches                                    | Momentary<br>with<br>Tactile Feel                          | 2A @ 28VDC<br>or 0.6mA @<br>15VDC<br>(logic level) | Water Resistant per<br>MIL-PRF-810F, Method<br>506.4 Procedure 3 (Drip)                   | 3/4" dia. Threaded                      | Two SPST (x2)                      |
| T2<br>(large)       | 2-Way,<br>Center Pushbutton<br>Option                         | Momentary<br>with<br>Tactile Feel                          | 10A @ 28VDC                                        | MIL-PRF-8805 -<br>Dusttight per Design 2,<br>Resilient per Design 4                       | Threaded or<br>Press Fit                | SPST, DPST<br>Double Break<br>(x3) |
| T4<br>(large)       | 4-Way                                                         | Momentary<br>with<br>Tactile Feel                          | 5A @ 30VDC                                         | MIL-PRF-8805 -<br>Dusttight per Design 2,<br>Resilient per Design 4                       | Press Fit                               | SPST (x4)<br>Multi-Pole<br>Option  |
| T5<br>(large)       | 4-Way plus<br>Center Pushbutton                               | Center<br>Maintained,<br>Momentary<br>with<br>Tactile Feel | 2A @ 28VDC                                         | MIL-PRF-8805 -<br>Dusttight per Design 2                                                  | Threaded or<br>Press Fit                | SPST (x5)<br>Multi-Pole<br>Option  |