



Power Turtle X CPTSX-T1-T7 (U.S.)

1x powerCON TRUE1 IN – 7x powerCON® TRUE1® TOP OUT - Indoor (NEMA1)

EU version: [Power Turtle X CPTX-T1-T7](#)



Power Turtle Xtreme Outdoor (XO) is a compact distribution solution for mobile applications. Rugged EASYLEN® housing is ideally suited for demanding applications and harsh conditions. 1x powerCON® TRUE1® TOP In and 7x powerCON® TRUE1® TOP Out.



Intertek

Features & Benefits

- Extreme robust and safe EASYLEN® housing with leather grain texture
- Flame retardant (UL94-V0) and non-conductive housing material
- Light weight, compact, lower height (Power Turtle) and stackable housing design
- Highly reliable NEUTRIK® powerCON® TRUE1® TOP recepticals for In, Out and Daisy chaining
- High mechanical protection (high IK)
- Versatile mounting options

Market & Application

- Markets. Professional video wall / lighting / audio
- Mobile application. Festivals, live events
- Semi-permanent applications. Theaters, studios

Article order data

Article name	Details	Order code
CPTSX-T1-T7	IN: powerCON® TRUE1® TOP OUT: 7x powerCON® TRUE1® TOP Indoor (NEMA1)	1035610

Technical Information

Product	
Input device	1x powerCON® TRUE1® TOP
Output device	7x powerCON® TRUE1® TOP
Daisy chaining	1x powerCON® TRUE1® TOP

Electrical	
Contact resistance / protection class	Protection class II
Dielectric strength	0.5 kV / mm
Rated voltage	120V AC
Rated Current	20A
Number of electrical contacts	2 + PE
Phases	single-phase

Mechanical	
Lifetime	> 5000 Mating cycles
Dimensions	220 x 150 x 65 mm
Conductor cross section	AWG12
Weight	1.0 kg
Mounting options	Truss clamp, mounting wholes for pegging or suspension
Type of construction	Stackable

Material	
Housing	Easylen
Color	black

Environmental	
Standards compatibility	UL94-V0
Protection class	NEMA1 listed. IP20.
Temperature range	-25 °C to +70 °C

Compliance	
Standard Compliance	ETL Listed. Compliant to UL STD 1640