

T9602 Humidity & Temperature Probe

The Telaire T9602 is a unique over molded Relative Humidity and Temperature probe with IP67 protection.

- Highly competitive for customers considering designing RH/T products with environmental protection.
- Available as standard with 1 or 1.8 meter cable and JST connector.
- IP67 protection – Total protection from dust and immersion upto 1 meter of water.

Features

- Fully Calibrated & Temperature Compensated
- ChipCap2 sensor
- Digital or Analogue Output
- IP67 Rated
- Precision & Accuracy ($\pm 2\%$ RH, $\pm 0.3^\circ\text{C}$, 14 bit)
- Low Current Consumption
- Reliable in Harsh Environments
- Different Mounting Options
- Multiple connectors or flying leads available



Applications

- HVAC – OEM Rooftops units.
- HVAC – Heat Exchangers.
- HVAC – Outside air transmitters.
- Automotive – Heavy truck/tractor cabin.
- Agriculture – Greenhouse & indoor growing.
- Industrial – Weather stations.



Ordering information

- [See datasheet](#) for part numbers. CPO required for further options.
- Sample requests email
Danielle.m.nelson@amphenol-sensors.com
- Technical support
Neil.S.Roberts@Amphenol-sensors.com
- Pricing
Chris.Ranwell@amphenol-sensors.com