

PRECISION RF CABLE CONNECTORS



COMPATIBILITY GUIDE FOR INDUSTRY STANDARD CABLES

Samtec offers a variety of precision, high-frequency cable connectors that are specifically designed to terminate to cables commonly used within the RF microwave/millimeter wave industry. Samtec's cable connectors are manufactured with a precise tolerance interface to ensure superior repeatability and high mechanical stability. Visit the Series page on [samtec.com](https://www.samtec.com) for access to prints with termination instructions.

SERIES	PRF10	PRF13	PRF18	PRF24	PRF92	PRF35	PRFS1	PRF01	PRFM0	PRF00	PRF06	PRF04
TYPE	1.00 mm	1.35 mm	1.85 mm	2.40 mm	2.92 mm	3.50 mm	SSMA	SMA	SMPM	SMP	N Type	TNCA

110 GHz - 1.00 mm - CABLE CONNECTORS				SERIES: PRF10	
	Part Number	Interface	Termination	Industry Standard Cable	
	PRF10-J-C-VP-047D-SS	1.00 mm Straight, Jack	Solder Clamp	.047 Semi-Rigid	
	PRF10-P-C-VP-047D-SS	1.00 mm Straight, Plug	Solder Clamp	.047 Semi-Rigid	
90 GHz - 1.35 mm - CABLE CONNECTORS				SERIES: PRF13	
	Part Number	Interface	Termination	Industry Standard Cable	
	PRF13-J-C-VP-047A-BS	1.35 mm Straight, Bulkhead Jack	Solder Clamp	Temp-Flex 1000671047	
	PRF13-P-C-VP-047A-SS	1.35 mm Straight, Plug	Solder Clamp	Temp-Flex 1000671047	
65 GHz - 1.85 mm - CABLE CONNECTORS				SERIES: PRF18	
	Part Number	Interface	Termination	Industry Standard Cable	
	PRF18-J-C-EP-085-BS	1.85 mm Straight, Bulkhead Jack	Solder Clamp	Harbour SS405	
	PRF18-P-C-EP-085-SS	1.85 mm Straight, Plug	Solder Clamp	Harbour SS405	
	PRF18-P-C-EE-085-SD	1.85 mm Straight, Plug	Direct Solder	Harbour SS405	
	PRF18-J-C-EP-086-SS	1.85 mm Straight, Jack	Solder Clamp	Temp-Flex 1001935086	
	PRF18-P-C-EP-086-SS-1	1.85 mm Straight, Plug	Solder Clamp	Temp-Flex 1001935086	
	PRF18-J-C-EP-047A-SS	1.85 mm Straight, Jack	Solder Clamp	Temp-Flex 1000671047	
	PRF18-P-C-EP-047A-SS	1.85 mm Straight, Plug	Solder Clamp	Temp-Flex 1000671047	
	PRF18-J-C-EP-047D-SS	1.85 mm Straight, Jack	Solder Clamp	.047 Semi-Rigid	
	PRF18-P-C-EP-047D-SS	1.85 mm Straight, Plug	Solder Clamp	.047 Semi-Rigid	
	PRF18-P-C-EE-047D-SD	1.85 mm Straight, Plug	Direct Solder	.047 Semi-Rigid	
	PRF18-P-C-EE-047H-SD	1.85 mm Straight, Plug	Direct Solder	EZ-47-LA Semi-Rigid	
	PRF18-P-C-EP-070-SD	1.85 mm Straight, Plug	Direct Solder	EZ-70-LA Semi-Rigid	
	PRF18-J-C-EE-405-SD	1.85 mm Straight, Jack	Direct Solder	RG 405 Semi-Rigid	
	PRF18-P-C-EE-405-SD	1.85 mm Straight, Plug	Direct Solder	RG 405 Semi-Rigid	
	PRF18-P-C-EP-086E-SS	1.85 mm Straight, Plug	Solder Clamp	Dynawave DF165	
50 GHz - 2.40 mm - CABLE CONNECTORS				SERIES: PRF24	
	Part Number	Interface	Termination	Industry Standard Cable	
	PRF24-J-C-EP-085-SS	2.40 mm Straight, Jack	Solder Clamp	Harbour SS405	
	PRF24-P-C-EP-085-SS	2.40 mm Straight, Plug	Solder Clamp	Harbour SS405	
	PRF24-P-C-EE-085-SD	2.40 mm Straight, Plug	Direct Solder	Harbour SS405	
	PRF24-J-C-EP-405-BS	2.40 mm Straight, Bulkhead Jack	Solder Clamp	RG 405	
	PRF24-P-C-EP-120A-SS	2.40 mm Straight, Plug	Solder Clamp	Semflex HP120	
	PRF24-J-C-EP-160-SS	2.40 mm Straight, Jack	Solder Clamp	Semflex HP160	
	PRF24-P-C-EP-160-SS	2.40 mm Straight, Plug	Solder Clamp	Semflex HP160	
	PRF24-J-C-EP-140B-SS	2.40 mm Straight, Jack	Solder Clamp	IW 1401	
	PRF24-P-C-EP-140B-SS	2.40 mm Straight, Plug	Solder Clamp	IW 1401	
	PRF24-J-C-EP-150B-SS	2.40 mm Straight, Jack	Solder Clamp	IW 1501	
	PRF24-P-C-EP-150B-SS	2.40 mm Straight, Plug	Solder Clamp	IW 1501	
	PRF24-J-C-EP-150-SS	2.40 mm Straight, Jack	Solder Clamp	Dynawave DF150	
	PRF24-P-C-EE-047D-SD	2.40 mm Straight, Plug	Direct Solder	.047 Semi-Rigid	
	PRF24-J-C-EP-047A-SS	2.40 mm Straight, Jack	Solder Clamp	Temp-Flex 1000671047	
	PRF24-P-C-EP-047A-SS	2.40 mm Straight, Plug	Solder Clamp	Temp-Flex 1000671047	
	PRF24-J-C-EP-086-SS	2.40 mm Straight, Jack	Solder Clamp	Temp-Flex 1001935086	
	PRF24-P-C-EP-086-SS	2.40 mm Straight, Plug	Solder Clamp	Temp-Flex 1001935086	
	PRF24-P-C-EE-086-SD	2.40 mm Straight, Plug	Direct Solder	Temp-Flex 1001935086	
	PRF24-J-C-EP-150A-SS	2.40 mm Straight, Jack	Solder Clamp	Storm Accu-Test 150	
	PRF24-P-C-EP-150A-SS	2.40 mm Straight, Plug	Solder Clamp	Storm Accu-Test 150	
	PRF24-P-C-EP-150-SS	2.40 mm Straight, Plug	Solder Clamp	Dynawave DF150	
	PRF24-P-C-EP-086E-SS	2.40 mm Straight, Plug	Solder Clamp	Dynawave DF165	

Visit [samtec.com/RF](https://www.samtec.com/RF) or contact RFGroup@samtec.com for more information.

40 GHz - 2.92 mm - CABLE CONNECTORS

SERIES: PRF92



Part Number	Interface	Termination	Industry Standard Cable
PRF92-J-C-EE-405-4D	2.92 mm Jack, 4-Hole Flange	Direct Solder	RG 405 Semi-Rigid
PRF92-P-C-EE-405-SD-3	2.92 mm Straight Plug, Captivated Contact	Direct Solder	RG 405 Semi-Rigid
PRF92-P-C-EE-405-SD	2.92 mm Straight, Plug	Direct Solder	RG 405 Semi-Rigid
PRF92-J-C-EP-402-SS	2.92 mm Straight, Jack	Solder Clamp	RG 402
PRF92-P-C-EE-402-SD	2.92 mm Straight, Plug	Direct Solder	RG 402
PRF92-P-C-EP-150B-SS	2.92 mm Straight, Plug	Solder Clamp	IW 1501
PRF92-P-C-EP-180B-SS	2.92 mm Straight, Plug	Solder Clamp	IW 1801
PRF92-J-C-EP-160-SS	2.92 mm Straight, Jack	Solder Clamp	Semflex HP160
PRF92-P-C-EP-160-SS	2.92 mm Straight, Plug	Solder Clamp	Semflex HP160
PRF92-P-C-EP-190-SS	2.92 mm Straight, Plug	Solder Clamp	Semflex HP190
PRF92-P-C-EP-175-SS	2.92 mm Straight, Plug	Solder Clamp	Semflex LA 180S
PRF92-P-C-EP-120A-SS-1	2.92 mm Straight, Plug	Solder Clamp	Semflex HP120S
PRF92-P-C-EP-120A-SS	2.92 mm Straight, Plug	Solder Clamp	Semflex HP120
PRF92-P-C-EE-085A-SD	2.92 mm Straight, Plug	Direct Solder	.085 Semi-Rigid
PRF92-J-C-EP-085-SS	2.92 mm Straight, Jack	Solder Clamp	Harbour SS405
PRF92-J-C-EP-085-BS	2.92 mm Straight, Bulkhead Jack	Solder Clamp	Harbour SS405
PRF92-P-C-EP-085-SS	2.92 mm Straight, Plug	Solder Clamp	Harbour SS405
PRF92-P-C-EP-160A-SS	2.92 mm Straight, Plug	Solder Clamp	Harbour LL160-40GHz
PRF92-P-C-EP-142-SS	2.92 mm Straight, Plug	Solder Clamp	Harbour LL142
PRF92-P-C-EP-086E-SS	2.92 mm Straight, Plug	Solder Clamp	Dynawave DF165
PRF92-P-C-EP-135-SS	2.92 mm Straight, Plug	Solder Clamp	Dynawave DF440W
PRF92-P-C-EP-140-SS	2.92 mm Straight, Plug	Solder Clamp	Dynawave DF140
PRF92-J-C-EP-047D-SS	2.92 mm Straight, Jack	Solder Clamp	.047 Semi-Rigid
PRF92-J-C-EP-047D-4S	2.92 mm Jack, 4-Hole Flange	Solder Clamp	.047 Semi-Rigid
PRF92-P-C-EP-047D-SS	2.92 mm Straight, Plug	Solder Clamp	.047 Semi-Rigid
PRF92-P-C-EE-047D-SD	2.92 mm Straight, Plug	Direct Solder	.047 Semi-Rigid
PRF92-P-C-EE-118-SD	2.92 mm Straight, Plug	Direct Solder	Haverhill HC35004
PRF92-P-C-EP-140C-SS	2.92 mm Straight, Plug	Solder Clamp	Times 510-0064
PRF92-P-C-EP-200-SS	2.92 mm Straight, Plug	Solder Clamp	Times MaxGain 200
PRF92-P-C-EE-118A-SD	2.92 mm Straight, Plug	Direct Solder	EZ-118 Semi-Rigid
PRF92-P-C-EE-086D-SD	2.92 mm Straight, Plug	Direct Solder	EZ-86-LA Semi-Rigid
PRF92-P-C-EE-047H-SD	2.92 mm Straight, Plug	Direct Solder	EZ-47-LA Semi-Rigid
PRF92-P-C-EP-086-SS-1-X	2.92 mm Straight, Plug	Solder Clamp	Temp-Flex 1001935086
PRF92-P-C-EP-130-SS	2.92 mm Straight, Plug	Solder Clamp	Temp-Flex 1001935130
PRF92-P-C-EP-135A-SS	2.92 mm Straight, Plug	Solder Clamp	Armored A89TK
PRF92-P-C-EE-120D-SD	2.92 mm Straight, Plug	Direct Solder	UT-120C-LL Semi-Rigid
PRF92-P-C-EP-135B-SS	2.92 mm Straight, Plug	Solder Clamp	Lab-Flex 160S
PRF92-P-C-EP-130A-SS	2.92 mm Straight, Plug	Solder Clamp	Micro-Coax UFA147A

34 GHz - 3.50 mm - CABLE CONNECTORS

SERIES: PRF35



Part Number	Interface	Termination	Industry Standard Cable
PRF35-P-C-EP-405-SS	3.50 mm Straight, Plug	Solder Clamp	RG 405 Semi-Rigid
PRF35-J-C-EP-402-BS	3.50 mm Straight, Bulkhead Jack	Solder Clamp	RG 402, .141, semi-rigid
PRF35-J-C-EP-402-SS	3.50 mm Straight, Jack	Solder Clamp	RG 402, .141, semi-rigid
PRF35-P-C-EP-402-SS	3.50 mm Straight, Plug	Solder Clamp	RG 402, .141, semi-rigid
PRF35-P-C-EP-120A-SS	3.50 mm Straight, Plug	Solder Clamp	Semflex HP120
PRF35-J-C-EP-160-SS	3.50 mm Straight, Jack	Solder Clamp	Semflex HP160
PRF35-P-C-EP-160-SS	3.50 mm Straight, Plug	Solder Clamp	Semflex HP160
PRF35-P-C-EP-210A-SS	3.50 mm Straight, Plug	Solder Clamp	Micro-Coax UFA210A

34 GHz - SSMA - CABLE CONNECTORS

SERIES: PRFS1



Part Number	Interface	Termination	Industry Standard Cable
PRFS1-J-C-EE-405-BD	SSMA Straight, Bulkhead Jack	Direct Solder	RG 405, Semi-Rigid
PRFS1-P-C-EE-405-SD	SSMA Straight, Plug	Direct Solder	RG 405, Semi-Rigid
PRFS1-P-C-EP-141A-SS	SSMA Straight, Plug	Solder Clamp	Harbour SS402

Visit [samtec.com/RF](https://www.samtec.com/RF) or contact RFGroup@samtec.com for more information.

18 GHz & 26.5 GHz - SMA - CABLE CONNECTORS

SERIES: PRF01



Part Number	Interface	Termination	Industry Standard Cable
PRF01-P-C-EP-120C-SS	SMA Straight, Plug	Solder Clamp	Harbour LL120
PRF01-J-C-EP-142-SS	SMA Straight, Jack	Solder Clamp	Harbour LL142
PRF01-P-C-EP-142-SS	SMA Straight Plug	Solder Clamp	Harbour LL142
PRF01-P-C-EP-142-SS-2	SMA Straight Plug, Vented Body	Solder Clamp	Harbour LL142
PRF01-P-C-EP-142-RS	SMA Right-Angle, Plug	Solder Clamp	Harbour LL142
PRF01-P-C-EP-142-RS-1	SMA Right-Angle Plug, with Lock-Wire Holes	Solder Clamp	Harbour LL142
PRF01-P-C-EP-142A-SS	SMA Straight, Plug	Solder Clamp	Harbour SB142
PRF01-P-C-EP-335-SS	SMA Straight, Plug	Solder Clamp	Harbour LL335
PRF01-J-C-EP-335A-SS	SMA Straight, Jack	Solder Clamp	Harbour LL335i
PRF01-J-C-EP-335A-BS	SMA Straight, Bulkhead Jack	Solder Clamp	Harbour LL335i
PRF01-P-C-EP-335A-SS	SMA Straight, Plug	Solder Clamp	Harbour LL335i
PRF01-P-C-EP-335A-SS-1	SMA Straight Plug, Low Profile	Solder Clamp	Harbour LL335i
PRF01-P-C-EP-335A-RS	SMA Right-Angle, Plug	Solder Clamp	Harbour LL335i
PRF01-J-C-EP-142-BS	SMA Straight, Bulkhead Jack	Solder Clamp	Harbour LL142
PRF01-J-C-EP-160A-BS	SMA Straight, Bulkhead Jack	Solder Clamp	Harbour LL160
PRF01-P-C-EP-160A-SS	SMA Straight, Plug	Solder Clamp	Harbour LL160-40 GHz
PRF01-P-C-EP-160A-RS	SMA Right-Angle, Plug	Solder Clamp	Harbour LL160
PRF01-P-C-EP-141A-SS	SMA Straight, Plug	Solder Clamp	Harbour SS402
PRF01-P-C-EP-141A-RS	SMA Right-Angle, Plug	Solder Clamp	Harbour SS402
PRF01-P-C-EP-088-SS	SMA Straight, Plug	Solder Clamp	Harbour SB316
PRF01-J-C-EP-190-SS	SMA Straight, Jack	Solder Clamp	Semflex HP190
PRF01-P-C-EP-190-SS	SMA Straight, Plug	Solder Clamp	Semflex HP190
PRF01-P-C-EP-190-SS-1	SMA Straight Plug, 26.5 GHz Version	Solder Clamp	Semflex HP190
PRF01-P-C-EP-190-RS	SMA Right-Angle, Plug	Solder Clamp	Semflex HP190
PRF01-J-C-EP-190-BS-1	SMA Straight, Bulkhead Jack	Solder Clamp	Semflex HP190
PRF01-P-C-EP-160-SS	SMA Straight, Plug	Solder Clamp	Semflex HP160
PRF01-P-C-EP-160-RS	SMA Right-Angle, Plug	Solder Clamp	Semflex HP160
PRF01-P-C-EP-305-SS	SMA Straight, Plug	Solder Clamp	Semflex HP305
PRF01-P-C-EP-290-SS	SMA Straight, Plug	Solder Clamp	Semflex LA290
PRF01-P-C-EP-290-SS-2	SMA Straight Plug, Low Profile	Solder Clamp	Semflex LA290
PRF01-P-C-EP-290-SS-3	SMA Straight Plug, with Lock-Wire Holes	Solder Clamp	Semflex LA290
PRF01-J-C-EE-405-SD	SMA Straight, Jack	Direct Solder	RG 405, Semi-Rigid
PRF01-P-C-EE-405-RD	SMA Right-Angle, Plug	Direct Solder	RG 405 Semi-Rigid
PRF01-P-C-EE-405-SD	SMA Straight, Plug	Direct Solder	RG 405 Semi-Rigid
PRF01-P-C-EE-402-SD	SMA Straight Plug, 18 GHz Version	Direct Solder	RG 402
PRF01-P-C-EE-047D-SD-1	SMA Straight Plug, 18 GHz Version	Direct Solder	.047 Semi-Rigid
PRF01-P-C-EE-047D-SD	SMA Straight Plug, 26.5 GHz Version	Direct Solder	.047 Semi-Rigid
PRF01-J-C-EE-047D-4D	SMA Straight Jack, 4-Hole Flange	Direct Solder	.047 Semi-Rigid
PRF01-J-C-EE-047D-SD	SMA Straight Jack, 26.5 GHz Version	Direct Solder	.047 Semi-Rigid
PRF01-J-C-EE-085A-4D	SMA Straight Jack, 4-Hole Flange	Direct Solder	.085 Semi-Rigid
PRF01-P-C-EP-090-SS	SMA Straight, Plug	Solder Clamp	Times AA-11288
PRF01-P-C-EP-290A-SS	SMA Straight, Plug	Solder Clamp	Times HF-290
PRF01-P-C-EP-200-SS	SMA Straight, Plug	Solder Clamp	Times Max Gain 200
PRF01-P-C-EP-300A-SS-01	SMA Straight, Plug	Solder Clamp	Times Max Gain 300
PRF01-P-C-EP-120B-SS	SMA Straight, Plug	Solder Clamp	IW 1201
PRF01-P-C-EP-180B-RS	SMA Right-Angle, Plug	Solder Clamp	IW1801
PRF01-P-C-EP-180BS-SS	SMA Straight, Plug	Solder Clamp	IW1801
PRF01-P-C-EP-150-SS	SMA Straight, Plug	Solder Clamp	Dynawave DF150
PRF01-P-C-EP-086E-SS	SMA Straight, Plug	Solder Clamp	Dynawave DF165 Cable
PRF01-P-C-EP-140D-SS	SMA Straight, Plug	Solder Clamp	Dynawave DX141
PRF01-P-C-EP-270A-RS	SMA Right-Angle, Plug	Solder Clamp	Dynawave DF218
PRF01-P-C-EP-135-RS	SMA Right-Angle, Plug	Solder Clamp	Dynawave DF440W
PRF01-P-C-EP-135-SS	SMA Straight, Plug	Solder Clamp	Dynawave DF440W
PRF01-P-C-EE-047B-SD	SMA Straight, Plug	Direct Solder	Temp-Flex 1001935047

65 GHz - SMPM - CABLE CONNECTORS

SERIES: PRFM0



Part Number	Interface	Termination	Industry Standard Cable
PRFM0-J-C-EE-085-BD	SMPM Straight, Bulkhead Jack	Direct Solder	Harbour SS405
PRFM0-J-C-EE-047A-BD	SMPM Straight, Bulkhead Jack	Direct Solder	Temp-Flex 1000671047
PRFM0-J-C-HG-047A-SD	SMPM Straight, Jack	Direct Solder	Temp-Flex 1000671047
PRFM0-J-C-EE-047A-RD	SMPM Right-Angle, Jack	Direct Solder	Temp-Flex 1000671047
PRFM0-P-C-HG-047A-SD	SMPM Straight, Full Detent Plug	Direct Solder	Temp-Flex 1000671047
PRFM0-J-C-EE-047B-SD	SMPM Straight, Jack	Direct Solder	Temp-Flex 1001935047
PRFM0-J-C-EE-086-SD	SMPM Straight, Jack	Direct Solder	Temp-Flex 1001935086
PRFM0-P-C-EE-086-SD	SMPM Straight, Plug	Direct Solder	Temp-Flex 1001935086

Visit samtec.com/RF or contact RFGroup@samtec.com for more information.

40 GHz - SMP - CABLE CONNECTORS

SERIES: PRF00



Part Number	Interface	Termination	Industry Standard Cable
PRF00-J-C-EE-047A-RD	SMP Right-Angle, Jack	Direct Solder	Temp-Flex 1000671047
PRF00-J-C-EE-085A-SD	SMP Straight, Jack (.264 long)	Direct Solder	.085 Semi-Rigid
PRF00-PF-C-KK-047D-BD	SMP Straight, Full Detent Plug, Bulkhead	Direct Solder	.047 Semi-Rigid

18 GHz - N Type - CABLE CONNECTORS

SERIES: PRF06



Part Number	Interface	Termination	Industry Standard Cable
PRF06-P-C-EP-141A-SS	N Type Straight, Plug	Solder Clamp	Harbour SS402
PRF06-J-C-EP-142-BS	N Type Straight, Bulkhead Jack	Solder Clamp	Harbour LL142
PRF06-P-C-EP-142-SS	N Type Straight, Plug	Solder Clamp	Harbour LL142
PRF06-P-C-EP-142-SS-1	N Type Straight Plug, Knurl-Hex Coupling Nut	Solder Clamp	Harbour LL142
PRF06-P-C-EP-142-RS	N Type Right-Angle, Plug	Solder Clamp	Harbour LL142
PRF06-P-C-EP-142A-SS	N Type Straight, Plug	Solder Clamp	Harbour SB142
PRF06-J-C-EP-335-BS	N Type Straight, Bulkhead Jack	Solder Clamp	Harbour LL335
PRF06-P-C-EP-335-SS	N Type Straight, Plug	Solder Clamp	Harbour LL335
PRF06-P-C-EP-335-RS	N Type Right-Angle, Plug	Solder Clamp	Harbour LL335
PRF06-P-C-EP-335-RS-1	N Type Right-Angle Plug, with Lock-Wire Holes	Solder Clamp	Harbour LL335
PRF06-J-C-EP-335A-BS	N Type Straight, Bulkhead Jack	Solder Clamp	Harbour LL335i
PRF06-P-C-EP-335A-SS	N Type Straight, Plug	Solder Clamp	Harbour LL335i
PRF06-P-C-EP-335A-RS	N Type Right-Angle, Plug	Solder Clamp	Harbour LL335i
PRF06-J-C-EP-160A-BS	N Type Straight, Bulkhead Jack	Solder Clamp	Harbour LL160
PRF06-P-C-EP-160A-SS	N Type Straight, Plug	Solder Clamp	Harbour LL160
PRF06-P-C-EP-160A-RS	N Type Right-Angle, Plug	Solder Clamp	Harbour LL160
PRF06-P-C-EP-120A-SS	N Type Straight, Plug	Solder Clamp	Semflex HP120
PRF06-J-C-EP-190-BS	N Type Straight, Bulkhead Jack	Solder Clamp	Semflex HP190
PRF06-P-C-EP-190-SS	N Type Straight, Plug	Solder Clamp	Semflex HP190
PRF06-P-C-EP-190-RS	N Type Right-Angle, Plug	Solder Clamp	Semflex HP190
PRF06-J-C-EP-290-BS	N Type Straight, Bulkhead Jack	Solder Clamp	Semflex LA290
PRF06-P-C-EP-290-SS	N Type Straight, Plug	Solder Clamp	Semflex LA290
PRF06-P-C-EP-290-SS-1	N Type Straight Plug, Enhanced Captivation	Solder Clamp	Semflex LA290
PRF06-P-C-EP-290-SS-2	N Type Straight Plug, Knurl-Hex Coupling Nut	Solder Clamp	Semflex LA290
PRF06-P-C-EP-290-RS	N Type Right-Angle, Plug	Solder Clamp	Semflex LA290
PRF06-P-C-EP-305-SS	N Type Straight, Plug	Solder Clamp	Semflex HP305
PRF06-J-C-EP-402-4S	N Type Straight Jack, 4-Hole Flange	Solder Clamp	RG 402, .141, semi-rigid
PRF06-P-C-EP-300A-SS	N Type Straight, Plug	Solder Clamp	Times Max Gain 300
PRF06-P-C-EP-180B-SS	N Type Straight, Plug	Solder Clamp	IW 1801
PRF06-P-C-EP-135-SS	N Type Straight, Plug	Solder Clamp	Dynawave DF440W
PRF06-P-C-EP-270A-RS	N Type Right-Angle, Plug	Solder Clamp	Dynawave DF218
PRF06-P-C-EP-160B-SS	N Type Straight, Plug	Solder Clamp	ATM CF-210
PRF06-P-C-EP-135B-SS	N Type Straight, Plug	Solder Clamp	Lab-Flex 160S
PRF06-P-C-EP-284-SS	N Type Straight, Plug	Solder Clamp	Micro-Coax UFB311A

18 GHz - TNCA - CABLE CONNECTORS

SERIES: PRF04



Part Number	Interface	Termination	Industry Standard Cable
PRF04-J-C-EP-142-BS	TNCA Straight, Bulkhead Jack	Solder Clamp	Harbour LL142
PRF04-P-C-EP-142-SS	TNCA Straight, Plug	Solder Clamp	Harbour LL142
PRF04-P-C-EP-142-RS	TNCA Right-Angle, Plug	Solder Clamp	Harbour LL142
PRF04-P-C-EP-160A-SS	TNCA Straight, Plug	Solder Clamp	Harbour LL160
PRF04-P-C-EP-335-SS	TNCA Straight, Plug	Solder Clamp	Harbour LL335
PRF04-P-C-EP-335-SS-1	TNCA Straight Plug, Knurl-Hex Coupling Nut	Solder Clamp	Harbour LL335
PRF04-J-C-EP-335A-BS	TNCA Straight, Bulkhead Jack	Solder Clamp	Harbour LL335i
PRF04-P-C-EP-335A-SS	TNCA Straight, Plug	Solder Clamp	Harbour LL335i
PRF04-P-C-EP-335A-RS	TNCA Right-Angle, Plug	Solder Clamp	Harbour LL335i
PRF04-J-C-EP-190-BS	TNCA Straight, Bulkhead Jack	Solder Clamp	Semflex HP190
PRF04-P-C-EP-190-SS	TNCA Straight, Plug	Solder Clamp	Semflex HP190
PRF04-P-C-EP-190-RS	TNCA Right-Angle, Plug	Solder Clamp	Semflex HP190
PRF04-P-C-EP-290-SS	TNCA Straight, Plug	Solder Clamp	Semflex LA290
PRF04-P-C-EP-290-SS-01	TNCA Straight Plug, Knurl-Hex Coupling Nut	Solder Clamp	Semflex LA290
PRF04-J-C-EP-270A-BS	TNCA Straight, Bulkhead Jack	Solder Clamp	Dynawave DF218
PRF04-J-C-EP-270A-BS-1	TNCA Straight, Bulkhead Jack, Extended Panel	Solder Clamp	Dynawave DF218
PRF04-P-C-EP-135-SS	TNCA Straight, Plug	Solder Clamp	Dynawave DF440W
PRF04-P-C-EP-200-SS	TNCA Straight, Plug	Solder Clamp	Times Max Gain 200
PRF04-P-C-EP-300A-SS	TNCA Straight, Plug	Solder Clamp	Times Max Gain 300
PRF04-J-C-EP-210A-BS	TNCA Straight, Bulkhead Jack	Solder Clamp	Micro-Coax UFA210A
PRF04-P-C-EP-210A-SS	TNCA Straight, Plug	Solder Clamp	Micro-Coax UFA210A
PRF04-P-C-EP-284-SS	TNCA Straight, Plug	Solder Clamp	Micro-Coax UFB311A
PRF04-J-C-EP-127-4S	TNCA Straight Jack, 4-Hole Flange	Solder Clamp	Storm VSR150

Visit samtec.com/RF or contact RFGroup@samtec.com for more information.