

Upgrade now from HDMI 1.4 to HDMI 2.0

with StarTech.com HDMI2-CABLE-4K60 Series



Premium High Speed HDMI

Certified for performance and reliability

- Certified Premium HDMI Cable for 4K at 60Hz, HDR, and 18Gbps bandwidth.
- Verified reliability over uncertified cables that may underperform.
- The preferred choice for enterprise IT Pros and AV integrators.



Engineered for Durability | Built to Last Through Thousands of Uses



- Gold-plated connectors rated for 10,000+ insertion cycles
- Bend-tested to 2,000 cycles at $\pm 60^\circ$, built for tight bends.
- Braided shielding provides superior EMI protection.

- TPE (Thermoplastic Elastomer) jacket offers flexibility and resilience.
- More environmentally responsible alternative to traditional PVC.
- Halogen-free, RoHS-compliant: Safer for users and the environment.

Easy Cable Identification with Quick ID Markings

Easily identify the right cable every time with clearly labeled HDMI connectors that show supported performance, eliminating guesswork and troubleshooting.





HDMI2-CABLE-4K60-XX



HDMI 2.0



4K60 / 3840x2160 @ 60 Hz

18 Gbps

HDCP 2.2

HDR10

Up to 32 Channels and 1536 kHz Frequency



TPE with Etched-In Performance Specs

Enhanced Strain Relief

Gold

TPE

1, 3, 6, 10, 12, 15, 20, 25, 30, 35, 50

0.3, 0.5, 1, 1.5, 2, 3, 4, 5, 7, 10, 15

HDMMXX



HDMI 1.4



4K30 / 3840 x 2160 @ 30 Hz

10.2 Gbps

HDCP 1.4



Up to 8 Channels and 192 kHz Frequency



PVC

Minimal Strain Relief

Gold

PVC

1, 3, 6, 8, 10, 12, 15, 20, 25, 30, 35, 40, 45, 50

0.3, 0.5, 1, 1.5, 2, 3, 5, 7, 10, 15

HDMI Standard

HDMI Certified

Maximum Resolution

Bandwidth

HDCP Support

HDR Support

Audio Support

ARC Support

Connector Design

Strain Relief

Connector Plating

Cable Jacket

Lengths (ft)

Lengths (m)



Quickly find the right connectivity accessory. Speak with an expert 24/5 at [startech.com/support](https://www.startech.com/support)

StarTech.com