



High Performance Certified Cables



“The clear labeling, durable construction, and reliable performance make them a must-have for IT professionals” **Mac Source**



USB4 Cables



Thunderbolt 5 Cables



240W Charging Cables

Backwards Compatibility

USB-C
Thunderbolt 3

Thunderbolt 4/3
USB4 / USB-C

PD 3.0 Charging
Any PD Device requiring <240W

Certification

USB-IF

Thunderbolt

USB-IF

Data Speed

40Gbps

80Gbps
(120Gbps w/ speed boost)

480Mbps

Maximum Resolution

8K 120hz
4K 240hz

8K 120hz
4K 240hz

No Video

Power Delivery

PD 3.1 – 240W

PD 3.1 – 240W

PD 3.1 – 240W

Jacket Material

TPE

TPE

Silicone with Braided Nylon

Available Lengths

1.6ft/50cm
50C-40G-USB4-CABLE [↗](#)
3.3ft/1m
1M-40G-USB4-CABLE [↗](#)

1.6ft/50cm
TBLT5MM50CM240W [↗](#)
2.6ft/80cm
TBLT5MM80CM240W [↗](#)
3.3ft/1m
TBLT5MM1M240W [↗](#)

3ft/91cm
S2CEPR3F-USB-CABLE [↗](#)
6ft/1.8m
S2CEPR6F-USB-CABLE [↗](#)
10ft/3m
S2CEPR10F-USB-CABLE [↗](#)



Quickly find the right connectivity accessory. Speak with an expert 24/5 at startech.com/support

StarTech.com